

Pipe Hanger 3265

Size (D) In.	Weight Lbs	Galvanized Steel	Carbon Steel	304SS
		14ga	7ga	16ga
3	0.40	Std		Std
4	0.45			
5	0.50			
6	0.60			
7	0.65			
8	0.75			
9	0.85			
10	.95			
11	1.00			
12	1.10			
13	1.20			
14	1.15			
15	1.30			
16	1.35			
17	1.40			
18	1.50			
20	1.80			
22	4.10			
24	5.00			
26	6.10	Std		
28	6.50			
30	6.90			
32	7.30			
34	7.70			
36	8.10			
38	8.50			
40	8.90			

Temperature Rating of Product Components		
° F	Pipe Hanger	
600°	Galvanized Steel	Optional - 304SS
500°		
390°		
158° (intermittent to 194°)		

Additional Notes

At temperatures ranging between 390° F and 480° F, the zinc-iron alloy layers in galvanized steel will continue to provide a high level of protection from corrosion. However, there may be some peeling, changes in mechanical properties, and reduction in the corrosion protection. Recommended max. service temperature is 390° F.

Compliance / Rating of Product Components		
Product	Material	Compliance / Rating
Pipe Hanger	Galvanized	ASTM A527 with a G-90 rating
	304SS	Finish meets ASTM A240
	316SS	Finish meets ASTM A240

Notes:

- Bolts and nuts supplied with hanger, size 5/16 -18 x 1-3/4" for hanger sizes 3" - 24" and size 3/8 -16 x 1-3/4" for hanger sizes 26" and up.

