

Ultra High Speed Floor Finish

Ultra High Speed Floor Finish is a high performance acrylic floor finish specifically designed for use for all floor high speed buffing and burnishing programs. Ideal for frequent burnishing programs and is optimized for the speed and pad pressure of propane machines. It will provide a long-lasting mark resistant finish with a brilliant deep gloss. Use on resilient tile, terrazzo, and other floors that are frequently buffed and burnished. Easy to apply, dries quickly for rapid recoating. Superior durability, gloss, and mark resistance.

DIRECTIONS

Read the entire label and SDS for proper use, handling and storage before using this product.

Application: For best results, floors should be clean and/or old coatings removed and the floor neutralized.

1. Apply finish in full uniform coats.
2. Allow to dry before recoating.
3. For maximum performance, apply additional coats of finish until the desired level of appearance and protection is achieved.
4. Allow to dry thoroughly for several hours before reopening up area for traffic.

Buffing: This finish can be repeatedly high speed buffed/burnished. Allow to dry thoroughly before buffing.

Stripping: This finish can be removed using a high quality Global stripping solution.

USE WITH GLOBAL FLOOR CARE MACHINES

- 261990 - Global Industrial™ Electric Auto Floor Scrubber 20" Cleaning Path - Corded
- 641244 - Global Industrial™ Auto Floor Scrubber 20" Cleaning Path, Two 115 Amp Batteries
- 641245 - Global Industrial™ Auto Ride-On Floor Scrubber 34" Cleaning Path, Three 170 Amp Batteries
- 641250 - Global Industrial™ Electric Auto Floor Scrubber 18" Cleaning Path - Corded
- 641251 - Global Industrial™ 17" Floor Machine
- 641252 - Global Industrial™ 20" Floor Machine
- 641253 - Global Industrial™ 20" Floor Machine, Dual Speed
- 641263 - Global Industrial™ Auto Floor Scrubber 18" Cleaning Path, Two 115 Amp Batteries
- 641264 - Global Industrial™ Auto Floor Scrubber 20" Cleaning Path, Two 115 Amp Batteries
- 641265 - Global Industrial™ Auto Floor Scrubber 26" Cleaning Path, Two 115 Amp Batteries
- 641310 - Global Industrial™ 20" Floor Burnisher
- 641311 - Global Industrial™ 20" Floor Burnisher W/ Dust Control



GLOBAL FACTS

- Brilliant gloss
- Optimized for frequent burnishing programs
- Mark resistant
- Durable
- Fast dry and recoat cycle

MARKETS

- Building Service Contractors
- Retail
- Education
- Healthcare
- Hospitality & Lodging

SPECIFICATIONS

Color	Opaque White
Scent	Acrylic
pH	8.0 - 9.0
Solid Content	22%

REORDER

640403 4x1 Gallons/Case

COMPARE TO

Global Catalog	Franklin Aurora (B260175)
Global Catalog	Franklin Interstate 50 (B56902)
Global Catalog	Franklin Quasar (B56905)
Global Catalog	Simoniz Ultra Line 33 (B639162)
Betco	Hi-Tech, Express
Diversey	Signature, Vectra
Spartan	Upper Limits



Global Industrial
2505 Mill Center Parkway, Buford, GA 30518
800-645-1232 • www.globalindustrial.com
Refer to SDS for more information.