

# 14"

# HIGH VELOCITY FAN



standard  
**YM - YOKE MOUNT**

additional mounting options:



PS - Pedestal Stroller



CW - Column Wall



TC - Truck Cooler



RM - Rack Mount



PB - Pedestal Base

Shipping Weights:

80 lbs/ 36 kg

64 lbs/ 29 kg

58 lbs/ 26 kg

49 lbs/ 22 kg

48 lbs/ 22 kg

SIZE	CFM	HP	FAN DIMENSIONS			DISTANCE AIR THROW	SHIPPING WEIGHT
			W	D	I.D.		
14"	2600	1/4	20"	16"	14.625"	60' / 18 m	42 lbs/ 19 kg

**Propeller:** 14" Diameter, 3 Blade GalvAlum (37 Degree)  
**Fan Inlet/Outlet:** High Impact Polypropylene  
**Finger Guards:** OSHA Standard, Spiral Wound Steel  
**RPM:** 1725  
**Decibels:** 66.5 @ 20'

**Enclosure:** TEAO Standard  
**Frame:** 48  
**Ambient Temperature:** 40C  
**Duty Cycle:** Continuous  
**Power Cord (115V Only):** 12' Length  
**Coverage:** 1800 Sq.Ft. Max  
**Warranty:** 2 Years

Voltage	Motor Amps	Running Amps
115V/ 208-230V*	2.8/ 1.4	2.8/ 1.4
208-230/ 460V	1.5-1.4/ .75	1.4/ .70
277V	1.1	1.1

\* standard

