

# 22"

# HIGH VELOCITY FAN



STANDARD  
**YM - YOKE MOUNT**

ADDITIONAL MOUNTING OPTIONS:



**RM** Rack Mount

57 lbs



**CW** Column-Wall

62 lbs



**PS** Portable Stroller

85 lbs



**PB** Pedestal Base

61 lbs

**SHIPPING WEIGHTS:**

SIZE	CFM	HP	FAN DIMENSIONS			AIR THROW DISTANCE	SHIPPING WEIGHT
			W	D	ID		
22"	5570	1/2	29"	16"	22.5"	100'	49 lbs

## FEATURES

- Propeller:** 21" Diameter, 3 Blade GalvAlum, 19°
- Fan Inlet/Outlet:** High Impact Polypropylene
- Finger Guards:** OSHA Compliant, Spiral Wound Steel
- Power Cord (115V Only):** 12' Length
- RPM:** 1725
- Decibels:** 73.6 @ 20' - 81.2 @ 3'
- Coverage:** 3600 ft<sup>2</sup>


**Warranty:** 2 Years

## MOTOR

VOLTAGE	MOTOR AMPS	RUNNING AMPS
115V/208-230V*	6.0/3.0-2.9	5.9/2.9-2.8
208-230/460V	2.4-2.3/1.2	2.3-2.2/1.1
277V	1.85	1.75

- Enclosure:** TEAO Standard
- Frame:** 56
- Ambient Temperature:** 104°F
- Duty Cycle:** Continuous

\*standard



## AIR FLOW PATTERN

Above velocities shown in feet/minute.