

TOTE & DEF TOTE HEATERS

Powerblanket® *Tote Heaters* maintain optimal heating conditions for temperature sensitive materials.

HERE'S HOW

- Distribute heat evenly around the tote
- Designed to be durable and weather resistant
- Provide easy access with a removable top
- Include an adjustable thermostatic controller
- Safely heat and protect a wide variety of chemicals and materials

Powerblanket® DEF Tote Heaters are temperature specific for the Diesel Exhaust Fluid to protect from freezing and maintain optimal temperatures.

- Fully enclose and heat the tote and pump housing unit
- 330 gallon version features flap to easily access pump
- Internal thermostats keep product temperature in spec
- Customized DEF bulk storage tanks available upon request

"Upon the implementation of using our new DEF system to stay compliant with EPA regulations, Powerblanket® provided an effective and energy efficient freeze protection system with its DEF Tote Heater System. We installed the unit and forgot about it, knowing our product is being protected, which gives us peace of mind."

— Jerri Brumfield

STANDARD SIZES fit the IBC 275 gallon (1,000 liter), 330 gallon (1,250 liter), 350 gallon (1,325 liter) 450 gallon (1,325 liter), 550 Gallon (1,325 liter) totes. **Other models, sizes and custom totes available upon request.**

READY TO SHIP



330 GALLON TOTE HEATER

powerblanket®

Product Category	Model #	Temperature Control	Approximate Product Temp*	Container Volume Size	Container Dimensions	Plug Type	AC Voltage	Wattage (+/-5%)	Amps	Approximate Weight/ Mass
IBC TOTE HEATERS	TH250	Programmable Digital Controller	up to 145° F (+ 5° F) / 63° C (+ 3° C)	250 Gallon / 950 L	48"L x 42"W x 35"H	15 AMP Plug	120V	1033	8.60	39 lbs / 18 kg
	TH250-240V	Programmable Digital Controller	up to 145° F (+ 5° F) / 63° C (+ 3° C)	250 Gallon / 950 L	48"L x 42"W x 35"H	15 AMP Plug	240V	1650	6.80	39 lbs / 18 kg
	TH275	Programmable Digital Controller	up to 145° F (+ 5° F) / 63° C (+ 3° C)	275 Gallon / 1040 L	48"L x 40"W x 46"H	15 AMP Plug	120V	1440	12.00	41 lbs / 19 kg
	TH275-240V	Programmable Digital Controller	up to 145° F (+ 5° F) / 63° C (+ 3° C)	275 Gallon / 1000 L	48"L x 40"W x 46"H	15 AMP Plug	240V	2400	10.00	41 lbs / 19 kg
	TH330	Programmable Digital Controller	up to 145° F (+ 5° F) / 63° C (+ 3° C)	330 Gallon / 1250 L	48"L x 40"W x 53"H	15 AMP Plug	120V	1440	12.00	45 lbs / 20 kg
	TH330-240V	Programmable Digital Controller	up to 145° F (+ 5° F) / 63° C (+ 3° C)	330 Gallon / 1250 L	48"L x 40"W x 53"H	15 AMP Plug	240V	2400	10.00	45 lbs / 20 kg
	TH350	Programmable Digital Controller	up to 145° F (+ 5° F) / 63° C (+ 3° C)	350 Gallon / 1325 L	48"L x 42"W x 47"H	15 AMP Plug	120V	1440	12.00	47 lbs / 21 kg
	TH350-240V	Programmable Digital Controller	up to 145° F (+ 5° F) / 63° C (+ 3° C)	350 Gallon / 1325 L	48"L x 42"W x 47"H	15 AMP Plug	240V	2400	10.00	47 lbs / 21 kg
	TH450	Programmable Digital Controller	up to 145° F (+ 5° F) / 63° C (+ 3° C)	450 Gallon / 1325 L	48"L x 42"W x 59"H	15 AMP Plug	120V	1440	12.00	50 lbs / 23 kg
	TH450-240V	Programmable Digital Controller	up to 145° F (+ 5° F) / 63° C (+ 3° C)	450 Gallon / 1325 L	48"L x 42"W x 59"H	15 AMP Plug	240V	2400	10.00	50 lbs / 23 kg
	TH550	Programmable Digital Controller	up to 145° F (+ 5° F) / 63° C (+ 3° C)	550 Gallon / 1325 L	48"L x 42"W x 71"H	15 AMP Plug	120V	1440	12.00	53 lbs / 24 kg
	TH550-240V	Programmable Digital Controller	up to 145° F (+ 5° F) / 63° C (+ 3° C)	550 Gallon / 1325 L	48"L x 42"W x 71"H	15 AMP Plug	240V	2400	10.00	53 lbs / 24 kg
DEF TOTE HEATERS	TH275D	Internal Preset	70° F (+ 10° F) / 21° C (+ 5° C)	275 Gallon / 1000 L	48"L x 40"W x 46"H	15 AMP Plug	120V	1440	12.00	100 lbs / 45 kg
	TH330D	Internal Preset	70° F (+ 10° F) / 21° C (+ 5° C)	330 Gallon / 1250 L	48"L x 40"W x 53"H	15 AMP Plug	120V	1440	12.00	105 lbs / 48 kg

330 GALLON DEF TOTE HEATER



350 GALLON TOTE HEATER AND THERMOSTATIC CONTROLLER

The leader in total temperature control, Powerblanket's high technology smart controls and monitoring devices, heating blankets, and chilling products solve a wide range of temperature problems. With Powerblanket, equipment lasts longer, projects stay on track, and fluids flow smoothly. Use Powerblanket year round to achieve total temperature control.

PHONE: 844.773.6169

FAX: 866.245.9483

EMAIL: INFO@POWERBLANKET.COM

3130 SOUTH 1030 WEST, SUITE 1

SALT LAKE CITY, UT 84119

WWW.POWERBLANKET.COM