



SAFETY DATA SHEET

Revision Date 22-Apr-2015

Version 1

1. IDENTIFICATION

Product identifier

Product Name Spray Nine® 1 gal

Other means of identification

Product Code 26801

Synonyms None

Recommended use of the chemical and restrictions on use

Recommended Use Disinfectant Cleaning

Uses advised against No information available

Details of the supplier of the safety data sheet

Manufacturer Address

ITW Permatex
10 Columbus Blvd.
Hartford, CT 06106 USA

Distributor

ITW Permatex Canada
35 Brownridge Road, Unit 1
Halton Hills, ON Canada L7G 0C6
Telephone: (800) 924-6994

Company Phone Number 1-87-Permatex
(877) 376-2839

24 Hour Emergency Phone Number Chem-Tel: 800-255-3924
International Emergency:
00+1+ 813-248-0585
Contract Number: MIS0003453

E-mail address mail@permatex.com

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status

This chemical is not considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Label elements

Emergency Overview

The product contains no substances which at their given concentration, are considered to be hazardous to health

Appearance Clear

Physical state Liquid

Odor Citrus

Hazards not otherwise classified (HNOC)

Not applicable

Other Information

Not applicable

3. COMPOSITION/INFORMATION ON INGREDIENTS

substance(s)

Chemical Name	CAS No	Weight-%	Trade Secret
WATER	7732-18-5	60 - 100	*
ETHOXYLATED C9-C11 ALCOHOLS	68439-46-3	1 - 5	*
DIPROPYLENE GLYCOL MONOBUTYL ETHER	29911-28-2	1 - 5	*

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES

Description of first aid measures

General advice	Get medical advice/attention if you feel unwell.
Eye contact	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
Skin contact	IF ON SKIN: Wash skin with soap and water. If skin irritation persists, call a physician. Wash contaminated clothing before reuse.
Inhalation	IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. If symptoms persist, call a physician.
Ingestion	IF SWALLOWED: Do NOT induce vomiting. Never give anything by mouth to an unconscious person. Call a physician.
Self-protection of the first aider	Use personal protective equipment as required. Avoid contact with skin, eyes or clothing.

Most important symptoms and effects, both acute and delayed

Symptoms See section 2 for more information.

Indication of any immediate medical attention and special treatment needed

Note to physicians Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media

Carbon dioxide (CO₂), Dry chemical, Foam

Unsuitable extinguishing media

None.

Specific hazards arising from the chemical

None in particular.

Explosion data

Sensitivity to Mechanical Impact None.
Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Ensure adequate ventilation, especially in confined areas. Avoid contact with eyes and skin. Use personal protective equipment as required.

Environmental precautions

Environmental precautions See Section 12 for additional ecological information.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Use personal protective equipment as required. Dam up. Cover liquid spill with sand, earth or other non-combustible absorbent material. Take up mechanically, placing in appropriate containers for disposal. Clean contaminated surface thoroughly.

Prevention of secondary hazards Clean contaminated objects and areas thoroughly observing environmental regulations.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Handle in accordance with good industrial hygiene and safety practice. Avoid breathing vapors or mists. Avoid contact with skin, eyes or clothing. Wash thoroughly after handling. Wash contaminated clothing before reuse. Use personal protective equipment as required.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place.

Incompatible materials Strong oxidizing agents

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

NIOSH IDLH Immediately Dangerous to Life or Health

Other Information Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992).

Appropriate engineering controls

Engineering Controls Showers
Eyewash stations
Ventilation systems

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Skin and body protection Wear protective gloves and protective clothing.

Respiratory protection Use NIOSH-approved air-purifying respirator with organic vapor cartridge or canister, as appropriate.

General Hygiene Considerations Handle in accordance with good industrial hygiene and safety practice. Regular cleaning of equipment, work area and clothing is recommended.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state	Liquid
Appearance	Clear
Odor	Citrus
Odor threshold	No information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	No information available	
Melting point / freezing point	No information available	
Boiling point / boiling range	100 °C / 212 °F	
Flash point	> 93 °C / > 200 °F	Tag Closed Cup
Evaporation rate	< 1	Butyl acetate = 1
Flammability (solid, gas)	No information available	
Flammability Limit in Air		
Upper flammability limit:	No information available	
Lower flammability limit:	No information available	
Vapor pressure	18 mm Hg	
Vapor density	>1	Air = 1
Relative density	1.02 g/ml	
Water solubility	Soluble in water	
Solubility in other solvents	No information available	
Partition coefficient	No information available	
Autoignition temperature	No information available	
Decomposition temperature	No information available	
Kinematic viscosity	No information available	
Dynamic viscosity	No information available	
Explosive properties	No information available	
Oxidizing properties	No information available	

Other Information

Softening point	No information available
Molecular weight	No information available
VOC Content (%)	<0.5%
Density	No information available
Bulk density	No information available

10. STABILITY AND REACTIVITY

Reactivity

No data available

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Conditions to avoid

Excessive heat.

Incompatible materials

Strong oxidizing agents

Hazardous Decomposition Products

Carbon oxides

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Inhalation	May cause irritation of respiratory tract.
Eye contact	Contact with eyes may cause irritation. May cause redness and tearing of the eyes.
Skin contact	May cause skin irritation and/or dermatitis.
Ingestion	Ingestion may cause irritation to mucous membranes.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
WATER 7732-18-5	> 90 mL/kg (Rat)	-	-
ETHOXYLATED C9-C11 ALCOHOLS 68439-46-3	= 1378 mg/kg (Rat) = 1400 mg/kg (Rat)	> 2 g/kg (Rabbit)	-
DIPROPYLENE GLYCOL MONONBUTYL ETHER 29911-28-2	= 1620 µL/kg (Rat)	= 5860 µL/kg (Rabbit)	= 42.1 ppm (Rat) 4 h

Information on toxicological effects

Symptoms No information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization No information available.
Germ cell mutagenicity No information available.
Carcinogenicity This product contains one or more substances which are classified by IARC as carcinogenic to humans (Group I), probably carcinogenic to humans (Group 2A) or possibly carcinogenic to humans (Group 2B).

The following values are calculated based on chapter 3.1 of the GHS document .

ATEmix (oral) 39421 mg/kg
ATEmix (dermal) 76980 mg/kg

12. ECOLOGICAL INFORMATION

Ecotoxicity

3.17% of the mixture consists of components(s) of unknown hazards to the aquatic environment

Chemical Name	Algae/aquatic plants	Fish	Crustacea
DIPROPYLENE GLYCOL MONONBUTYL ETHER 29911-28-2	-	841: 96 h Poecilia reticulata mg/L LC50 static	-

Persistence and degradability

No information available.

Bioaccumulation

No information available.

Mobility

No information available.

Other adverse effects

No information available

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal of wastes	Disposal should be in accordance with applicable regional, national and local laws and regulations.
Contaminated packaging	Do not reuse container.
US EPA Waste Number	Not applicable

14. TRANSPORT INFORMATION

DOT

Proper shipping name: Not regulated

IATA

Proper shipping name: Not regulated

IMDG

Proper shipping name: Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA	Complies
DSL/NDSL	Complies
EINECS/ELINCS	Not determined
ENCS	Not Listed.
IECSC	Complies
KECL	Not determined
PICCS	Not determined
AICS	Not determined

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

EINECS/ELINCS - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances

ENCS - Japan Existing and New Chemical Substances

IECSC - China Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

AICS - Australian Inventory of Chemical Substances

US Federal Regulations**SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Acute health hazard	Yes
Chronic Health Hazard	No
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product contains the following substances which are regulated pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302)

US State Regulations**California Proposition 65**

This product contains the following Proposition 65 chemicals

Chemical Name	California Proposition 65
ETHANOL - 64-17-5	Carcinogen Developmental

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
SODIUM HYDROXIDE 1310-73-2	X	X	X
ETHANOL 64-17-5	X	X	X

U.S. EPA Label Information

EPA Pesticide Registration Number 6659-3

EPA Statement

This chemical is a pesticide product registered by the Environmental Protection Agency and is subject to certain labeling requirements under federal pesticide law. These requirements differ from the classification criteria and hazard information required for safety data sheets, and for workplace labels of non-pesticide chemicals.

<u>NFPA</u>	Health hazards 1	Flammability 1	Instability 0	-
<u>HMIS</u>	Health hazards 1	Flammability 1	Physical hazards 0	Personal protection B

NFPA (National Fire Protection Association)

HMIS (Hazardous Material Information System)

Revision Date 22-Apr-2015

Disclaimer

The information provided in this Material Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet