

# PRODUCT DATA SHEET



**Model: DB212C**  
**12" Corded Inductor In-Line Duct Fan**  
800 Max Boosted CFM, 650 Free Air CFM  
120 Running Watts, 1.50 Amps, 120 VAC, 60 Hz  
UL® Listed  
1 Year Limited Warranty  
12" Diameter  
Assembled in the USA  
Primary UOM: EA  
Shipping Multiple: 2

## Performance

Max Boosted CFM	Free Air CFM	Watts	Amps	Volts	Hz	dBA	Sones
800	650	120	1.50	120	60	55	3

## Hazardous Material Info

Not Applicable

## Customs Tariff Classification

HS Code	Country of Origin	NAFTA Preference Criterion	NAFTA Producer Index
8414596090	USA	B	Y

## Packaging Metrics

	UPC/SCC	Width (in)	Height (in)	Depth (in)	Weight (lbs)
Unit	066028000842	8.50	12.75	12.50	
Master Case	40066028000840				