



WC-1HPMFAOSC

Portable Evaporative Cooler



Air Velocity (@ 10') :	1650	Housing Material :	ABS Plastic
Blade Color :	Gray	Nameplate Amps :	12.4
Blade Material :	Galvanized Steel	On Board Reservoir :	Yes
CFM (free air) :	3020	Oscillating :	Yes
CFM (high) :	3020	Schaefer Performance Test No. :	Schaefer
CFM (low) :	2040	Phase :	1
CFM Range (Free Air) :	2501 - 5000	Power (hp) :	1
CFM/Watt (free Air) :	4	Power (Voltage & Phase) :	115 Single Phase
Component Certifications :	Motor - UL/CSA	Product Color :	White
Cord :	Included - Wired	Product Weight (pounds) :	177
Cord Length (feet) :	9	Speed Control Compatible :	No
Country of Origin :	US	Speeds :	2
Distinguishing Feature :	Cools Air via Evaporative Cooling	Switch :	On product
Fixed or Portable :	Portable	VFD Compatible :	No
Frequency (Hz) :	60	Voltage :	115
Housing Color :	White		