



# SharkBite® Push-To-Connect Fittings

For Copper, CPVC or PEX Pipe

## DESCRIPTION

The SharkBite® Push-To-Connect (PTC) Fittings allow the user to connect pipe in seconds with relative ease.

## FEATURES AND BENEFITS

Instant push-fit connection for increased ease-of-use:  
*No soldering, clamps, unions, or glue required.*

Fittings certified to 200 PSI and 200°F (93°C):  
*Proven durability and quality.*

Fits copper tubing, and CTS CPVC and PEX:  
*Connects all three types in any combination.*

Integral pipe liner for PEX installations:  
*Integrated design means no loose components, ensures secure, reliable connection.*

Design certified and agency listed:  
*Inspector friendly, peace of mind!*

Compact, robust Lead Free DZR brass body:  
*Foundation of a strong, corrosion resistant, durable fitting.*

Design certified to NSF/ANSI 61, NSF/ASNI 14 and ASSE 1061 product standard for use in potable water and hydronic heating water distribution:  
*Quality engineered and manufactured.*

Approved to be used underground and behind walls without access panels.  
*Designed for hydronic heating as well as potable water distribution.*

## SPECIFICATION

The tube shall be inserted into the SharkBite PTC Fitting in the first stage through a release collar and then through a stainless steel grab ring. The grab ring has teeth that open out and grip onto the tube. At the second stage the tube shall be pushed through an O-ring protector which aligns the pipe. A specially formulated EPDM O-ring shall be compressed between the wall of the fitting and the tube before the end of the tube reaches the tube stop. Only when the pipe has passed through the O-ring and reached the pipe stop shall a secure joint be created. The fitting shall be a SharkBite PTC Fitting.



U008LF



U248LF



U362LF




# SharkBite® Push-To-Connect Fittings

For Copper, CPVC or PEX Pipe

## TYPICAL INSTALLATION


### Connecting a joint:



Push the pipe and fitting together firmly with a twisting action until it clicks. Allow at least 1" clearance between fittings for disconnection.

(Please consult with local plumbing codes concerning specific water heater piping requirements.)

### Disconnecting a joint:



Push the disconnect clip against the release collar and pull the pipe with a twisting action.

## SPECIFICATION DATA

### Performance:

Maximum working pressure . . . . . 200 psi  
 Maximum temperature . . . . . 200°F (93°C)  
 Service . . . . . Potable water

### Materials:

Body . . . . . DZR Lead Free Brass  
 O-ring . . . . . EPDM  
 Grab ring . . . . . Stainless steel  
 Tube support liner . . . . . Polysulfone

### Finish:


Natural Brass or Chrome Plated

Fitting Size	Insertion Depth
1/4"	0.813"
3/8"	0.875"
1/2"	0.938"
5/8"	1.125"
3/4"	1.125"
1"	1.313"

## CERTIFICATIONS


The SharkBite PTC Fittings have been designed certified and listed to ASSE 1061, NSF/ANSI 61, NSF/ANSI 14, and NSF/ANSI 372. The SharkBite PTC Fittings are listed by IAPMO and are certified for potable and hydronic heating water distribution (note: Glycol mixture for hydronics is acceptable up to 100% concentration). The SharkBite PTC Fittings have been certified for underground applications and as a manufactured joint without access panels and they meet UPC, IPC and cUPC requirements.






**Straight Coupling Dimensions**

P/N	A	B
U004LF	1/4"	1.59"
U006LF	3/8"	1.84"
U008LF	1/2"	2"
U016LF	3/4"	2.36"
U020LF	1"	2.72"




**Elbow Dimensions**

P/N	A	B	C
U244LF	1/4"	1/4"	1.160"
U276LF	1/4"	3/8" MIP	1.160"
U246LF	3/8"	3/8"	1.280"
U272LF	1/2"	3/8"	1.430"
U248LF	1/2"	1/2"	1.360"
U256LF	3/4"	3/4"	1.640"
U250LF	1"	1"	1.933"
U274LF	3/4"	1/2"	1.373"
U280LF	1/2"	1/2" MNPT	1.210"
U308LF	1/2"	1/2" FNPT	1.210"





**Reducing Coupling Dimensions**

P/N	A	B	C
U009LF	3/8"	1/2"	2.00"
U058LF	3/4"	1/2"	2.20"
U060LF	1"	3/4"	2.51"




**Tee Dimensions**

P/N	A	B	C	D
U358LF	1/4"	1/4"	1/4"	2.30"
U360LF	3/8"	3/8"	3/8"	2.77"
U362LF	1/2"	1/2"	1/2"	2.72"
U363LF	1/2"	1/2"	3/8"	2.85"
U364LF	3/8"	3/8"	1/2"	2.77"
U370LF	3/4"	3/4"	3/4"	3.24"
U374LF	1"	1"	1"	3.84"
U412LF	3/4"	3/4"	1/2"	3.04"
U416LF	1"	1"	3/4"	3.63"
U444LF	3/4"	1/2"	3/4"	3.08"
U454LF	3/4"	1/2"	1/2"	2.92"



**Connector Dimensions**


P/N	A	B	C
U066LF	1/4"	1/2" FNPT	1.61"
U068LF	1/2"	3/4" FNPT	1.75"
U070LF	3/8"	1/2" FNPT	1.73"
U072LF	1/2"	1/2" FNPT	1.64"
U092LF	3/4"	1/2" FNPT	1.83"
U088LF	3/4"	3/4" FNPT	1.88"
U094LF	1"	1" FNPT	2.17"
U110LF	1/4"	1/2" MNPT	1.64"
U118LF	3/8"	1/2" MNPT	1.77"
U120LF	1/2"	1/2" MNPT	1.64"
U116LF	1/2"	3/4" MNPT	1.75"
U134LF	3/4"	3/4" MNPT	1.89"
U138LF	3/4"	1/2" MNPT	1.90"
U140LF	1"	1" MNPT	2.48"
U142LF	1"	3/4" MNPT	2.11"



**Drop Ear Elbow Dimensions**


P/N	A	B	C
U249LF	1/2"	1/2"	2.20"
U332LF	3/8"	1/2" FNPT	1.83"
U334LF	1/2"	1/2" FNPT	1.77"
U335LF*	1/2"	1/2" FNPT	2.00"
U540LF	3/4"	3/4" FNPT	2.50"

\*Hy-Ear Elbow




**Fitting Reducer Dimensions**

P/N	A	B	C
U719LF	3/8"	1/2"	2.08"
U721LF	3/8"	3/4"	2.27"
U722LF	1/2"	1"	3"
U724LF	3/4"	1"	2.25"




**End Stops Dimensions**

P/N	A	B
U512LF	3/8"	1.11"
U514LF	1/2"	1.08"
U518LF	3/4"	1.32"
U520LF	1"	1.52"




**Fitting Adapter Dimensions**

P/N	A	B	C
U766LF	3/4" FNPT	3/4"	2.83"
U772LF	1" FNPT	1"	2.83"



**Disconnect Clips Dimensions**

P/N	Fits SharkBite	A	B	C
U711	1/2"	1.7"	2"	6.5"
U713	3/4"	1.7"	2"	6.5"
U715	1"	1.7"	2"	6.5"



**Slip Coupling\* Dimensions**

P/N	A	B	C
U3008LF	1/2"	1.075"	4.46"
U3016LF	3/4"	1.355"	4.42"
U3020LF	1"	1.640"	4.5"


\*For use with copper & CPVC only



**Disconnect Clip Dimensions**


P/N	Size	A	B
U706	1/4"	1.19"	0.3"
U708	3/8"	1.22"	0.3"
U710	1/2"	1.22"	0.3"
U712	3/4"	1.72"	0.4"
U714	1"	2"	0.4"

Note: Disconnect Clips sold separately




**Straight Stop (Chrome Plated) Dimensions**

P/N	A	B	C
23037-0000LF	1/2"	3/8" Compression	2.68"




**Ballcock Connector Dimensions (Chrome Plated)**

P/N	A	B	C
U3531LF	1/4"	7/8" Ballcock	1.58"




**Faucet Connector Dimensions (Chrome Plated)**

P/N	A	B	C
U3525LF	1/4"	1/2" NPS	1.58"




**Stop Connector Dimensions (Chrome Plated)**

P/N	A	B	C
U3523LF	1/4"	1/2" NPS	1.58"



**Angle Stop (Chrome Plated) Dimensions**

P/N	A	B	C
23036-0000LF	1/2"	3/8" Compression	2.58"



**Ballcock Elbow (Chrome Plated) Dimensions**

P/N	A	B	C
U3537LF	1/4"	7/8" Ballcock	1.05"

