


## AUDIO CABLE

### 14 AWG / 2 Conductor



#### Description

14/2 Stranded CMR/CL3R Sound Audio Cable

#### Applicable Standards

- For Communication and Signal Control Systems
- 2 Oxygen Free Bare Copper Conductors in an Overall Jacket

#### Physical Characteristics

Conductor		Oxygen Free B.C.
Number of Conductors		2
AWG		14
Stranding		105
Diameter	(inches)	0.0063
Insulation		PVC
Diameter	(inches)	0.1023
Average Thickness	(inches)	0.014
Min. Point Thickness	(inches)	0.013
<b>Assembly Diameter</b>		(inches) 0.2047
Jacket		PVC
Outer Diameter	(inches)	0.2519
Average Thickness	(inches)	0.0236
Min. Point Thickness	(inches)	0.02126
<b>Rip Cord</b>		<b>Nylon</b>
Conductor Resistance	(ohms)	9.2
Nominal Weight	(pounds)	22

#### Colors

Insulation Colors Black / Red

#### Part Numbers

Part Number	Color	Put-up
AC1402R-BL-1-500	Blue	500' PULL BOX
AC1402R-WH-1-500	White	500' PULL BOX

#### Cable Marking

AUDIO CABLE 2 COND 14AWG HI-STRAND OFC CMR/CL3R FT4 75C  
 XXXXXXX C(ETL)US \*\*\*\*FT