

Security Stranded Cable 22 AWG / 2 Conductor



Description

22/2 Stranded Bare Copper CMR Security Cable

Applicable Standards

- Class 2 Power Limited Circuit Cable and Communications
- Cable for General Purpose Applications

Physical Characteristics

Conductor		Stranded Bare Copper
Number of Strands		7
Number of Conductors		2
AWG		22
Insulation		PVC
Avg. Thickness	(inches)	0.006
Insulated Conductor Dia.	(inches)	0.041
Jacket		FR-PVC
Avg. Thickness	(inches)	0.014
Overall Diameter	(inches)	0.110
Nominal Weight	(pounds)	11

Colors

Insulation Colors	Green, Red
Jacket Color	White

Part Numbers

Part Number	Color	Put-up
SC2202RGY1-S	Grey	1,000' Box
SC2202RWH1-S	White	1,000' Box

Cable Marking

22AWG 2 COND STRANDED XXXXXXXX CMR/CL2 R FT4 C(ETL)US ****FT