



Light Duty



Cut-Protection

## Safety, durability and comfort combined

- HyFlex® 11-644 offers a dynamic mix of performance, durability and comfort.
- The ANSI Level 2 cut performance and lightweight ergonomic fit strike the perfect balance of protection and precision when working with small, sharp parts
- The HyFlex 11-644 glove with Ansell Cut Protection Technology is an effective way to decrease injury expenses without reducing productivity or quality. That's because it combines superior cut protection, abrasion resistance, grip, tactility, and dexterity in a comfortable glove your workers are more likely to wear



### Industries

- Aerospace
- Automotive
- Construction
- Electronics & Electrical
- Glass Products
- Metal Fabrication
- Paper Manufacturing
- Plastic & Rubber Manufacturing
- Public Utilities
- Tier One
- Transportation
- White/Durable Goods

### Applications

- Final & sub-assembly areas when handling metal components
- Glass handling & installations
- Forming, machining & bending small parts
- Small part stamping
- Wiring

#### Performance Profile

- Ansell Cut Protection Technology combines a proprietary blend of high performance polyethylene into differentiated engineered yarn for ANSI level 2 cut performance.
- Polyurethane coating provides ANSI level 5 abrasion performance and excellent resistance to tears. Tough coating provides a sure grip in light oil and dry applications. Gray palm color hides soil.
- Glove molds naturally to the hand and is soft and cool to the skin for all day comfort.
- The exceptional precision, dexterity, and flexibility when handling small, sharp parts increases worker confidence while on the job.


#### Key Features

- Enhanced cut protection, wear life, and comfort with a high level of dexterity.
- High dexterity with longer wear due to low palm weight and excellent abrasion resistance.
- Available in a broad range of sizes to fit all workers from 5-12 (XS-XXXL).

#### Technologies



#### Performance Standards



#### Specifications

BRAND   STYLE	DESCRIPTION	GAUGE	SIZE	LENGTH	COLOR	PACKAGE
HyFlex 11-644	Cut resistant multi-purpose glove: Ansell Cut Resistant Technology 13 gauge high performance polyethylene (HPPE) liner with polyurethane (PU) palm coating	13	5-12	207-277 mm 8.14-10.90 inches	Grey coating on white liner	12 pairs/polybag, 12 polybags/carton

#### Europe, Middle East & Africa

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
+32 2 528 74 00  
+32 2 528 74 01

#### North America

Ansell Healthcare Products, LLC  
111 Wood Avenue South  
Suite 210  
Iselin, NJ 08830, USA  
+1 800 800 0444  
+1 800 800 0445

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
+61 1800 337 041  
+61 1800 803 578

#### Asia Pacific

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
63000 Cyberjaya  
Selangor, Malaysia  
T: +60 3 83106688  
F: +60 3 8318 6699

#### Latin America & Caribbean

Ansell Brazil Ltda.  
Rua das Figueiras 474 - 4º Andar  
Bairro Jardim  
SP 09080-300 Santo André  
Brazil  
CNPJ: 03.496.778/0001-21  
+55 11 3356 3100

#### Russia

Анселл РУС  
123610 Россия, Москва  
Краснопресненская  
Наб. 12, п.3, оф. 1304А  
Тел. +7 495 258 13 16

Ansell, \* and TM are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2016 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.