

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-920

Light duty oil repellent,
oil grip multi-purpose glove



Light Duty



Oil-Repellent

High performance grip and oil repellence

- HyFlex 11-920 glove provide high performance grip and oil repellence when working in oily environments
- ANSELL GRIP™ Technology contains microscopic channels in the glove coating to displace oil, resulting for a more secure grip when handling oily parts
- RIPEL™ Liquid Repellence Technology creates a liquid-impermeable layer to prevents oil or lubricant from making contact with the wearer's skin, enhancing hand health
- Seamless knit design provide an outstanding fit, comfort and dexterity to maximize all-day productivity



Industries

- Aerospace
- Appliance Manufacturing
- Electronics Manufacturing
- Medical Laboratories
- Research Laboratories

Applications

- Assembling, inspecting and packing small or delicate parts
- Electrical component assembly and installation
- Final assembly areas

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-920

Light duty oil repellent,
oil grip multi-purpose glove

Performance Profile

- Patent-pending ANSELL GRIP Technology coating wicks oil away from the hand in microscopic channels.
- Increases surface contact for enhanced grip and control.
- Prevents oil penetration and reduces the risk of dermatitis and liquid exposure.
- Multi-layer coating provides high abrasion resistance and increases wear life.
- Ergonomic, natural fit along with superior dry and oil grip for high productivity.
- Durable material is machine launderable for extended life and reduced replacement costs.

Technologies

 **RIPEL™**
Liquid Repellence Technology

 **ANSELL GRIP™**
Ansell Grip Technology

Performance Standards



Specifications

BRAND STYLE	DESCRIPTION	GAUGE	SIZE	LENGTH	COLOR	PACKAGE
HyFlex 11-920	Type: Palm coated Coating material: Nitrile Liner material: Nylon Cuff style: Knitwrist	15	6-11	208-270 mm 8.18-10.62 inches	Blue	12 pairs/bag, 12 bags/carton

Europe, Middle East & Africa

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
+32 2 528 74 00
+32 2 528 74 01

North America

Ansell Healthcare Products, LLC
111 Wood Avenue South
Suite 210
Iselin, NJ 08830, USA
+1 800 800 0444
+1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
+61 1800 337 041
+61 1800 803 578

Asia Pacific

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
63000 Cyberjaya
Selangor, Malaysia
T: +60 3 83106688
F: +60 3 8318 6699

Latin America & Caribbean

Ansell Brazil Ltda.
Rua das Figueiras 474 - 4º Andar
Bairro Jardim
SP 09080-300 Santo André
Brazil
CNPJ: 03.496.778/0001-21
+55 11 3356 3100

Russia

Анселл РУС
123610 Россия, Москва
Краснопресненская
Наб. 12, п.3, оф. 1304А
Тел. +7 495 258 13 16

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2016 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.