

# Model 405

## Basic Weighing Scale



- **Accuracy**– Within  $\pm 3$  divisions at full load
- **Capacity**– 6 kg / 12 lb and 15 kg / 30 lb
- **Construction**– ABS plastic housing, stainless steel weight platter
- **Display**– Easy to read LED
- **Power**– AC and rechargeable battery for portability
- **Operator Keys**– Tare/Units, On/Off/Zero
- **Platform Size**– 215 mm x 245 mm / 8.5" x 9.5"

# 405 Basic Weighing Scale

## Features

The 405 general purpose scales offer exceptional value for your money. The 405 is very versatile, quickly changing from one application to another. The stainless steel platter is removable making it easy to clean. The red LED makes for easy readability in any indoor lighting condition. Included is a rechargeable internal battery with an auto off feature to preserve the life of the battery between charges.

The base is constructed of ABS plastic, which provides outstanding protection for daily usage and helps to lock out moisture.

The 405 features selectable lb, kg, gram, oz, lb/oz units and a tare feature. With a resolution of 1 g / 0.002 lb for the 6 kg / 12 lb model and 2 g / 0.005 lb for the 15 kg / 30 lb the 405 general purpose scales are accurate for any general weighing application.

A wipedown plastic cover comes standard to protect the display, keyboard and housing from dust and food particles.

## Specifications

### Capacity:

Model	lb	kg	grams	oz	lb/oz
405-6	12 x 0.002	6 x 0.001	6000 x 1	192 x 0.05	12 x 00.05
405-15	30 x 0.005	15 x 0.002	15000 x 2	480 x 0.1	30 x 00.1

### Display: LED

**Keyboard:** Tare/Units, On/Off/Zero

**Unit:** kg, g, lb, lb/oz, oz

**Power:** AC and rechargeable battery

**Battery Life:** 20 hours

**Operating Temperature:** 5° C - 35° C / 41° F - 95° F

### Platform Dimension:

215 mm x 245 mm / 8.5" x 9.5"

### Scale Dimension:

110 mm (H) x 255 mm (W) x 305 mm (L)  
4.25" H x 10" W x 12" L

### Packaging Dimension:

180 mm (H) x 385 mm (W) x 305 mm (L)  
7" H x 15" W x 12" L

**Shipping Weight:** 5 kg / 10 lb



a division of Avery Weigh-Tronix, LLC

### Brecknell

1000 Armstrong Dr., Fairmont, MN 56031  
Toll free: 800-637-0529, Tel: 507-238-8702  
Fax: 507-238-8271  
e-mail: sales@brecknell scales.com  
www.brecknell scales.com



### Brecknell

Foundry Lane, Smethwick  
West Midlands B66 2LP UK  
Tel: +44 (0) 845 246 6717  
Fax: +44 (0) 845 246 6718  
Email: sales@brecknell scales.co.uk  
www.brecknell scales.co.uk

