

# LPS-15

## Portable Bench Scale CE



*Shown with optional foot switch*

- **Accuracy**– 0.1% of full scale
- **Capacity**– 15 kg / 30 lb
- **Construction**– Low profile stainless steel platform with mild steel understructure, stainless steel/ABS indicator with wall bracket and desk mount included.
- **Platform Size**–  
380 mm (L) x 305 mm (H) x 27 mm (W)  
15" L x 12" W x 1" H
- **Display**– Five 16 mm / 0.625" digits LCD
- **Power**– Battery or AC power
- **Operator Keys**– On/Off/Zero, Tare, Units (lb, kg, lb/oz), Hold/Print,

# LPS-15 Portable Bench Scale

## Features

Portion control and product quality requirements make this economic scale perfect for use in pizza parlors, sandwich and salad shops, bakeries and supermarkets. Great for use in food operations to build consistent products and help control ingredient costs. Optional remote switch allows zeroing of the scale without using your hands.

The dual power modes (battery and AC adapter) enable portability or permanent installation (both included).

A large, simple to read display can be wall or stand mounted for easy visibility and the push button switches work with gloved hands (wall and desk mount included).

The indicator cable is a coil style for durability and easy extension to the wall or desk mount display.

The LPS-15 features a full-duplex RS-232 interface that can transmit and receive using a demand type protocol.

The durable low profile SST platform allows for easy weighing and cleanup. Although NOT suitable for washdown, this scale is perfect for an environment where wipe down sanitation is sufficient. The LPS-15 is a low cost, versatile and portable scale.



*Shown with optional foot switch*

## Specifications

**Capacity:** 15 kg x .005 kg / 30 lb x 0.01 lb/0.2 oz

**Display:** Five 16 mm / 0.625" digits LCD

**RS-232:** 10' interface cable (DB-9) (included)

**Keyboard:** On/Off/Zero, Tare, Units (kg/lb), Hold/Print

**Units:** lb, kg, lb/oz

**Power:** Four AAA batteries or 6 VDC, 500mA adapter (both included)



### Optional Power Adapter:

816965002887: UK

816965002870: EU

**Battery Life:** 20 hours

### Operating Temperature:

5° C to 35° C / 41° F to 95° F

### Platform Dimension:

380 mm (L) x 305 mm (H) x 27 mm (W)

15" L x 12" W x 1" H

### Indicator Dimension:

164 mm (L) x 81 mm (H) x 29 mm (W)

6.5" L x 3.2" H x 1.2" W

**Product Weight:** 4 kg / 9 lb

### Packaging Dimension:

Scale: 450 mm (L) x 400 mm (W) x 60 mm (H)

17" L x 15" W x 2.3" H

**Shipping Weight:** 5 kg / 11 lb

**Optional:** Foot Switch

**Certifications:** Full FCC compliance, UL/CUL power adapter

**Product Code:** 816965004799

**Packaging Contents:** RS-232 cable, power adapter, four AAA batteries, manual, platform with indicator and stand with misc hardware



a division of Avery Weigh-Tronix, LLC

### Brecknell

1000 Armstrong Dr., Fairmont, MN 56031  
Toll free: 800-637-0529, Tel: 507-238-8702  
Fax: 507-238-8271  
e-mail: sales@brecknell scales.com  
www.brecknell scales.com



### Brecknell

Foundry Lane, Smethwick  
West Midlands B66 2LP UK  
Tel: +44 (0) 845 246 6717  
Fax: +44 (0) 845 246 6718  
Email: sales@brecknell scales.co.uk  
www.brecknell scales.co.uk

