

MS-15

Medical/Veterinary Scale CE



- **Accuracy**– +/- 3 divisions
- **Capacity**– 20 kg / 44 lb
- **Construction**– ABS plastic with removable weighing tray
- **Display**– Bright, large and visible
- **Power**– Four AA Batteries (included)
- **Operator Keys**– On/Off/Tare, Units, Hold

VALUE IN
WEIGHING

MS-15 Medical/Veterinary Scale

Features

The MS-15 scale is particularly suited to the medical or veterinary industry. With a capacity of 20 kg / 44 lb and readability of 5 g / 0.005 lb, the MS-15 will accurately weigh infants or small animals.

The scale has a "HOLD" feature that will capture an unstable weight and keep it on the display for recording after the weight is taken off.

The LCD display has a blue backlight with standard features of kg and lb and a hold feature. Operates on four AA batteries (included).

Easy-to-clean plastic weighing platter.

Specifications

Capacity: 20 kg x 5 g / 44 lb x 0.005 lb

Weighing Range: 0.2 kg to 20 kg / 0.5 lb to 44 lb

Display: 25 mm / 1.0" LCD display with four active digits

Keyboard: On/Off/Tare, Unit, Hold

Power: Four AA alkaline battery (included)

Operating Temperature: 5° C to 35° C / 41° F to 95° F

Units: kg and lb

Tray: ABS plastic

Inside Tray Dimension:

584 mm (L) x 292 mm (W)

23" L x 11" W

Product Dimension:

578 mm (L) x 334 mm (W)

23" L x 13" W

Product Weight: 3 kg / 6.6 lb

Packaging Dimension:

635 mm (L) x 381 mm (W) x 152 mm (H)

25" L x 15" W x 6" H

Shipping Weight: 4 kg / 9 lb

Product Code: 816965005123

Packaging Contents: Scale and manual



a division of Avery Weigh-Tronix, LLC

Brecknell

1000 Armstrong Dr., Fairmont, MN 56031
Toll free: 800-637-0529, Tel: 507-238-8702
Fax: 507-238-8271
e-mail: sales@brecknellscales.com
www.brecknellscales.com



Brecknell

Foundry Lane, Smethwick
West Midlands B66 2LP UK
Tel: +44 (0) 845 246 6717
Fax: +44 (0) 845 246 6718
Email: sales@brecknellscales.co.uk
www.brecknellscales.co.uk

