

# MS140-300

## Portable Medical Electronic Handrail Scale

CE



- **Accuracy**– +/- 3 divisions (0.6 lb, 0.3 kg, 15 oz)
- **Capacity**– 660 lb x 0.2 lb; 300 kg x 0.1 kg; 660 lb x 5 oz
- **Construction**– Stainless steel weighing surface with mild steel foam covered handrails. Rigid base design.
- **Power**– 6 VDC, 500mA wall mount adapter (included)
- **Weight Hold**– May be used to freeze and store the displayed weight so that you may attend to the patient's needs
- **Integrated Wheel Kit**– For easy portability

VALUE IN  
WEIGHING

# MS140-300 Portable Medical Electronic Handrail Scale

## Features

Simplicity of design and rugged construction are the key features of the MS140-300 Portable Medical Scale.

Featuring a 520 mm (L) x 520 mm (W) / 20.5" x 20.5", low-profile (65 mm (H) / 2.5" H) platform with sturdy handrails and padded grips, the MS140-300 digital scale was designed to be the perfect choice for clinics, health clubs, or even home use.

This medical scale has the ability to print weight data offering a real time saving device for doctor's offices, long-term care facilities, and other medical institutions.

Heavy-duty, yet lightweight & portable this scale is suitable for almost any application requiring accuracy and medium to heavy weight capacity. The repeatability is unbeatable and will offer years of continued usage. It comes with an easy-to-read LCD backlit display and operates on AC power. This medical scale is durable and reliable at an affordable price.



## Specifications

<u>Capacity (lb)</u>	<u>Capacity (kg)</u>	<u>Capacity (lb/oz)</u>
660 lb x 0.2 lb	300 kg x 0.1 kg	660 lb x 5 oz

**Accuracy:** +/- 3 divisions (0.6 lb, 0.3 kg, 15 oz)

### Platform Dimension:

Scale: 520 mm (L) x 520 mm (W) x 1,135 mm (H)  
20.5" L x 20.5" W x 44.25" H

### Weighing Platform:

520 mm (L) x 520 mm (W) x 65 mm (H)  
20.5" L x 20.5" W x 2.5" H

**Display:** 17 mm / 0.625V high LCD

**Indicator:** 165 mm (L) x 30 mm (W) x 81 mm (H)  
6.5" L x 1.2 W x 3.2" H

**Serial Port:** One (1) full duplex RS232 with cable

**Function Keys:** Hold/Print, Units, Tare, On/Off/Zero

**Unit:** lb, kg, lb/oz

**Power:** 6 VDC, 500mA adapter (included)

**Optional Power Adapter:** UK 816965002887  
EU 816965002870

**Operating Temp:** 5° C to 35° C / 41° F to 95° F

**RS-232:** Supplied complete with 10' cable (9 pin to 9 pin type connector, bi-directional full duplex)

**Product Weight:** 19 kg / 42 lb

### Packaging Dimension:

1168 mm (L) x 635 mm (W) x 152 mm (H)  
46" L x 25" W x 6" H

**Shipping Weight:** 25 kg / 55 lb

**Packaging Contents:** Manual, platform, 3 piece handles, power supply, RS-232 cable, indicator, 3 hex wrenches and pull through string

**Approvals:** Full FCC compliance, UL/CUL power adapter

**Product Code:** 816965004829



a division of Avery Weigh-Tronix, LLC

## Brecknell

1000 Armstrong Dr., Fairmont, MN 56031  
Toll free: 800-637-0529, Tel: 507-238-8702  
Fax: 507-238-8271  
e-mail: sales@brecknellscales.com  
www.brecknellscales.com



## Brecknell

Foundry Lane, Smethwick  
West Midlands B66 2LP UK  
Tel: +44 (0) 845 246 6717  
Fax: +44 (0) 845 246 6718  
Email: sales@brecknellscales.co.uk  
www.brecknellscales.co.uk

