

PS-USB



Portable Shipping Scale



- **Capacity—**
15 kg x 0.005 kg / 30 lb x 0.01 lb
30 kg x 0.01 kg / 70 lb x 0.02 lb
60 kg x 0.02 kg / 150 lb x 0.05 lb
- **Units—** kg, lb, lb:oz* (*non-NTEP)
- **Display—** 6½ digits 25 mm / 1" high, seven segments LCD with blue backlight
- **Construction—** Heavy duty cast aluminum base with stainless steel platter
- **Power—** 6VDC 500mA adapter with center positive or four AA batteries
- **RS-232 and USB Interface**
- **Emulation Protocols:** Standard NCI default with field configurable settings of NCI, 8213, 3835 and Autosend. Interfaces with software programs such as UPS™ Worldship Online.
- **Platform Dimension—**
355 mm (W) x 305 mm (L) / 14" W x 12" L
- **Product Dimension—**
355 (W) x 411 mm (L) x 80 mm (H)
14" W x 16" L x 3.15" H

PS-USB Portable Shipping Scale

Features

PS-USB scales are particularly suited to shipping and warehouse applications and general purpose weighing. These are very affordable scales with high accuracy.

The triple power modes (battery, AC adapter and USB) enable portability or permanent installation.

The PS-USB features RS-232/USB interface that can transmit and receive using a demand type protocol.

Comes with adjustable feet and leveling bubble for precise weighing.



Removable stainless steel platter



Durable cast aluminum upper load cell supporter and cast aluminum base

Specifications

Capacity:

15 kg x 0.005 kg / 30 lb x 0.01 lb

30 kg x 0.01 kg / 70 lb x 0.02 lb

60 kg x 0.02 kg / 150 lb x 0.05 lb

Platform Dimension:

355 mm (W) x 305 mm (L) / 14" W x 12" L

Product Weight: 4.8 kg / 10.5 lb

Display: 6½ digits 25 mm / 1" high, seven segments LCD with blue backlight

RS-232/USB: Bi-directional full duplex (USB and RS-232 cable included)

Other Functions: Weighing, counting, check weighing, percent weighing, accumulation

Keyboard: Hold/setup, print/func, acc/total, unit/data, tare/preset, on/off/zero

Units: kg, lb, lb:oz

Power:

6VDC 500mA adapter (AWT05-507975 USA - included) with center positive

Four AA batteries (not included)

USB (VCP) cable (included)

Optional Power Supplies:

AWT05-507841: UK power adapter

AWT05-507842: EU power adapter

Battery Life: 20 hours

Operating Temperature: -10° C to 40° C / 14° F to 104° F

Packaging Dimension:

505 mm (L) x 465 mm (W) x 150 mm (H)

20" L x 18" W x 6" H

Shipping Weight: 6.3 kg / 14 lb

Certifications: NTEP CC# 15-084 / Measurement Canada AM-6006 (SBI-240), NTEP CC# 15-083 / Measurement Canada AM-5998 (PS-USB base)

Part Number:

816965006540: 15 kg / 30 lb

816965006533: 30 kg / 70 lb

816965006526: 60 kg / 150 lb



a division of Avery Weigh-Tronix, LLC

Brecknell

1000 Armstrong Dr., Fairmont, MN 56031

Toll free: 800-637-0529, Tel: 507-238-8702

Fax: 507-238-8271

e-mail: sales@brecknellscales.com

www.brecknellscales.com



Brecknell

Foundry Lane, Smethwick

West Midlands B66 2LP UK

Tel: +44 (0) 845 246 6717

Fax: +44 (0) 845 246 6718

Email: sales@brecknellscales.co.uk

www.brecknellscales.co.uk

