

INVACARE®
CHECK O₂ PLUS™
CONCENTRATOR ANALYZER



The **Invacare® Check O₂ Plus™ Concentrator Analyzer** is a single economical instrument that reports all the operating parameters necessary for performing oxygen concentrator checks. It is an efficient and cost-effective analyzer designed with technicians in mind. It checks oxygen concentration, flow rate and patient outlet pressure on any oxygen concentrator. What's more, it requires no routine calibration, and there's no fuel cell to replace. The Invacare Check O₂ Plus Concentrator Analyzer is three analyzers rolled into one.

Features

- Measures three parameters, eliminating the need for multiple instruments: oxygen purity, flow rate and patient outlet pressure
- Accurately measures oxygen purity of the Invacare® XPO₂™ Portable Concentrator
- Features simple two-button operation
- Two AA batteries provide over 16,000 readings
- Shuts off automatically to extend battery life
- Requires no in-field calibration
- Self-diagnostics
- Includes connecting tube and protective boot



Invacare Corporation
www.invacare.com

USA
One Invacare Way
Elyria, Ohio
44035-4190
(800) 333-6900

Canada
570 Matheson Blvd. E.,
Unit 8
Mississauga, Ontario
L4Z 4G4 Canada
(800) 668-5324

©2012
Invacare Corporation.
All rights reserved.
Trademarks are identified
by the symbols ™ and ©. All trademarks are
owned by or licensed
to Invacare Corporation
unless otherwise noted.
Specifications are subject
to change without
notification.
Form No. 12-295
120386



Model #	Weight	Quantity Per Case	Oxygen Flow	Pressure Range	Oxygen Range	Operating Temperature	Limited Warranty
IRC450	6.4 oz.	1	0-10 LPM ±.2%	.5-50 PSI ±.5%	21%-95.6% ±1.5%	59°-104° F (15°-40°C)	3 Years

