

AMFAB™



13080 H

TOP FINISH	H Base Opal Frame	
	W/O VANITY	UOM
Gunstock Walnut	13080 (stock item)	1/cs
Fusion Maple	13080-HOFM	1/cs
Banister Oak	13080-HOBO	1/cs
Wild Cherry	13080-HOWC	1/cs
English Oak	13080-HOEO	1/cs
Figured Mahogany	13080-HODM	1/cs
Nepal Teak	13080-HONT	1/cs
Quartered Oak	13080-HOQO	1/cs
Solar Oak	13080-HOSO	1/cs

Low Bed Overbed Table

Bariatric Overbed Table

Item #	UOM
13081	1/cs

- Designed specifically for use with low beds with 3.25" frame to floor clearance.
- Walnut woodgrain melamine top.
- Top can be raised or lowered in infinite settings between 19.5"- 27.5".
- Tabletop can be raised with the slightest upward pressure.
- The frame is constructed with tubular steel and durable, attractive chrome finish.
- Swivel casters allow for easy maneuverability.

specifications	
Height (adjustable)	19.5" - 27.5"
Weight	25 lbs.
Carton Shipping Weight	28 lbs.
Weight Limit	100 lbs.
Base Dimensions	15" x 28"
Tabletop Dimensions	50" x 30"
Warranty	Limited Lifetime

- Base and columns available in additional powder coat finishes.
- In the locked position, the table can support 500 lbs.
- Structurally reinforced with a steel-welded frame.
- Frame extends virtually the entire length of the top.
- Tabletop height adjusts from 30"- 45" in 1" increments.
- Large, high-pressure laminate table top measures 18" x 40" to reach the center line of most bariatric beds.
- Powder-coated base and column.
- 2" swivel casters make for easy maneuverability.

specifications	
Height (adjustable)	30" - 45"
Weight	70 lbs.
Carton Shipping Weight	75 lbs.
Weight Limit	500 lbs.
Base Dimensions	18" x 42"
Tabletop Dimensions	18" x 40"
Warranty	Limited Lifetime