



COMPARE TO
 Hoyer/Joerns® C-HCA
 Invacare® 9805

13023 - Sling
 Sold Separately



COMPARE TO
 Invacare® RPL450-1
 Graham Field® LF1040

Sling Sold Separately

Hydraulic Deluxe Chrome-Plated Patient Lift with 6-Point Cradle

Item #	Product Description	For Use With	UOM
13023			1/cs
13023CSET	3" Casters, Contains Two 3" Non-Locking Caster and Two 3" Locking Caster	Low Bed	4/bx

- Chrome-plated steel provides maximum strength.
- Safely raises or lowers individuals from any stationary position.
- 6 point Swivel Bar that can accommodate, 2 or 4 sling straps, plus 2 chain connections .
- High-performance hydraulics raise or lower individuals gradually and safely.
- Easy-to-operate caster brakes provide security.
- Includes sling chains.

specifications	
Boom Height	17.5" - 62"
Base Width	22.5" - 42"
Base Height	6"
Casters	5"
Weight	72 lbs.
Carton Shipping Weight	81 lbs.
Weight Limit	450 lbs.
Warranty	Limited Lifetime (frame), 1 Year Limited (pump)

Battery-Powered Patient Lift with 6-Point Cradle

Item #	UOM
13240	1/cs

- Heavy-gauge construction.
- Jumbo actuator pump with emergency button can switch to manual mode to lower patient down safely.
- Fast, easy charge from AC outlet.
- To charge, simply plug in unit. Battery does not need to be removed to be charged. Lift will not operate while plugged in. For home-care use.
- Audible warning when battery power falls below 50%.

specifications	
Boom Height	27.5" - 76"
Base Width	41" (open) 24" (closed)
Base Height	4.75"
Base Clearance	2"
Casters	5" Rear
Weight	108 lbs.
Carton Shipping Weight	122 lbs.
Weight Limit	450 lbs.
Warranty	Limited Lifetime
1 Year Electronics	Battery, Hand control, Actuator

replacement parts		
13240C	Charger for 13240	1/ea