



Bariatric Sentra EC Heavy-Duty, Extra-Extra-Wide Wheelchair Dual Cross Brace

HCPCS: K0007

- Carbon steel frame with triple-coated chrome for an attractive, chip-proof, maintainable finish
- Reinforced steel gussets at all weight bearing points provide additional strength
- Durable reinforced nylon upholstery
- Steel, spoke wheels are strong and maintenance free
- Heavy-duty, flat-free 8" front casters are adjustable in two positions
- Extra-heavy-duty front forks
- Reinforced side frame, caster journals and dual cross bars
- Precision sealed wheel bearings in front and rear ensure long-lasting performance and reliability
- Extra-large, padded armrests provide comfort and support
- Riggings have extra-large, heavy-duty, aluminum foot plates that provide maximum support, are attractive and crack proof (Must be ordered separately)
- Comes with push-to-lock wheel locks
- Weight Capacity 700 lbs

PRODUCTS

PRODUCTS	Description
STD26ECDDA	Sentra EC 26Det.DeskArm, 1/cs
STD26ECDFA	Sentra EC 26in Det.FullArm, 1/cs
STD28ECDDA	Sentra EC 28Det.DeskArm, 1/cs
STD28ECDFA	Sentra EC 28Det.FullArm, 1/cs
STD30ECDDA	Sentra EC 30Det.DeskArm, 1/cs
STD30ECDFA	Sentra EC 30Det.FullArm, 1/cs

SPECIFICATIONS

SPECIFICATIONS	Description
Width Open Closed with 26" Seat	34.5" 14"
Width Open Closed with 28" Seat	37" 14.5"
Width Open Closed with 30" Seat	39" 15"
Height	35"
Seat-To-Floor Height	19.5"
Back Height	18"
Seat Depth	20"
Length with Riggings	43"
Product Weight with 26" Seat	62 lbs.
Product Weight with 28" Seat	64 lbs.
Product Weight with 30" Seat	66 lbs.
Carton Shipping Weight with 26" Seat	68 lbs.
Carton Shipping Weight with 28" Seat	70 lbs.
Carton Shipping Weight with 30" Seat	72 lbs.
Weight Limit	700 lbs.

SPECIFICATIONS

Description

Warranty	Limited Lifetime
----------	------------------

ACCESSORIES

Description

STDS829	Anti-Tippers With Wheels, Chrome, 1/pr
STDS855	Seat Belts, Auto-Clasp Type Closure, Bariatric, 1/ea
STDS856	Seat Belts, Hook and Loop Fastener Type Closure, Bariatric, 1/ea
PH-SF	Aluminum Foot plate, 1/pr
PHELRL	Aluminum Foot plate, 1/pr
STDS831	Heel Loops, 1/bx
STDS820	Telescoping IV Pole Attachment, 1/ea
STDS803	Universal Oxygen "E" Cylinder Holder, 1/ea
STDS804	Universal Oxygen "E" Cylinder Holder with IV Pole Attachment, 1/ea
STDS801	Wheel Lock Extension, 1/ea
STDS1034	Wheelchair Cane/Crutch Holder, 1/ea

PARTS

Description

STDS829	Anti-Tippers With Wheels, Chrome, 1/pr
STDS855	Seat Belts, Auto-Clasp Type Closure, Bariatric, 1/ea
STDS856	Seat Belts, Hook and Loop Fastener Type Closure, Bariatric, 1/ea
PH-SF	Aluminum Foot plate, 1/pr
PHELRL	Aluminum Foot plate, 1/pr
STDS831	Heel Loops, 1/bx
STDS820	Telescoping IV Pole Attachment, 1/ea
STDS803	Universal Oxygen "E" Cylinder Holder, 1/ea
STDS804	Universal Oxygen "E" Cylinder Holder with IV Pole Attachment, 1/ea
STDS801	Wheel Lock Extension, 1/ea
STDS1034	Wheelchair Cane/Crutch Holder, 1/ea
STDS1M2206	1/ea
STDS1M2208	1/ea
STDS1M2213	1/ea
STDS1M2201	1/ea
STDS1M2205-8	
STDS1M2200	1/ea
STDS1M2202-2	
STDS1M2203	1/ea
STDS1M2204	1/ea
STDS1M22X6	1/ea
STDS1M22X7	1/ea
STDS1M2210	1/ea
STDS1M2209-2	
STDS1M2212	1/ea
STDS1M2214	1/ea
STDS1M2215	1/ea
STDS1M2226	1/ea
STDS1M2228	1/ea
STDS1M2230	1/ea
STDS4027R	1/ea
STDS4027L	1/ea
STDS55B	
STDS1M2211	1/ea
STDS1M2221	1/ea
STDS1M2222	1/ea
STDS1M2218	1/ea
STDS1M2219-14	