

# NOW AVAILABLE!

## LOW CAPACITY AND LOWER COST V-GRIP™ 20 SHELVING

Equipto has expanded its V-Grip™ shelving line to now offer a lighter capacity and lower cost solution for your storage needs. V-Grip™ 20 is the offspring of Equipto's traditional industrial grade shelving that now gives the flexibility to customize your inventory management systems. V-Grip™ 20 uses 20-gauge steel for its shelves. The product is otherwise identical to the original V-Grip™ with options including:

- Back and Side Panels
- Drawers
- Sliding Dividers
- Full Height, Half Height, and Clear View Doors



Equipto continues to revolutionize its products to provide infinite and unlimited utility to expand, adapt, and change with your needs anytime.

### V-Grip™ 20 Solid Shelving, Open, 84”H

Depth	Width	Shelf Capacity	5 Shelves Starter	Add-On	7 Shelves Starter	Add-On	Extra Shelf
<b>12” Depth</b>							
12”	36”	225 lbs	261-5S	261-5A	261-7S	261-7A	2230
12”	42”	175 lbs	261Y5S	261Y5A	261Y7S	261Y7A	2250
12”	48”	150 lbs	261W5S	261W5A	261W7S	261W7A	2240
<b>18” Depth</b>							
18”	36”	225 lbs	263-5S	263-5A	263-7S	263-7A	2231
18”	42”	175 lbs	263Y5S	263Y5A	263Y7S	263Y7A	2251
18”	48”	150 lbs	263W5S	263W5A	263W7S	263W7A	2241
<b>24” Depth</b>							
24”	36”	225 lbs	265-5S	265-5A	265-7S	265-7A	2232
24”	42”	175 lbs	265Y5S	265Y5A	265Y7S	265Y7A	2252
24”	48”	150 lbs	265W5S	265W5A	265W7S	265W7A	2242
<b>36” Depth</b>							
36”	36”	225 lbs	267-5S	267-5A	267-7S	267-7A	2234

### V-Grip™ 20 Solid Shelving, Closed, 84”H

Depth	Width	Shelf Capacity	5 Shelves Starter	Add-On	7 Shelves Starter	Add-On	Extra Shelf
<b>12” Depth</b>							
12”	36”	225 lbs	271-5S	271-5A	271-7S	271-7A	2230
12”	42”	175 lbs	271Y5S	271Y5A	271Y7S	271Y7A	2250
12”	48”	150 lbs	271W5S	271W5A	271W7S	271W7A	2240
<b>18” Depth</b>							
18”	36”	225 lbs	273-5S	273-5A	273-7S	273-7A	2231
18”	42”	175 lbs	273Y5S	273Y5A	273Y7S	273Y7A	2251
18”	48”	150 lbs	273W5S	273W5A	273W7S	273W7A	2241
<b>24” Depth</b>							
24”	36”	225 lbs	275-5S	275-5A	275-7S	275-7A	2232
24”	42”	175 lbs	275Y5S	275Y5A	275Y7S	275Y7A	2252
24”	48”	150 lbs	275W5S	275W5A	275W7S	275W7A	2242
<b>36” Depth</b>							
36”	36”	225 lbs	277-5S	277-5A	277-7S	277-7A	2234

# INDUSTRIAL V-GRIP™ SHELVING

As the industry leader in structural integrity, Equipto's traditional 18-gauge V-Grip™ shelving was engineered to provide maximum load-bearing capabilities. The V-Grip™ upright posts have an exclusive triangular design that provides a smooth front surface without unsightly holes or hardware. The V-Grip™ Clip's allow the shelving system components to be adjustable for convenient reconfiguration and accommodates high-rising applications to reduce wasted overhead space. This allows you to expand your space utilization options when more storage is needed by adding V-Grip™ to:

- Mobile Aisles
- Deck-Over Systems
- Multi-Level Systems



V-Grip™ Solid Shelving, Open, 84”H

Depth	Width	Shelf Capacity	5 Shelves Starter	5 Shelves Add-On	7 Shelves Starter	7 Shelves Add-On	Extra Shelf
<b>12” Depth</b>							
12”	36”	650 lbs	661-5S	661-5A	661-7S	661-7A	6230
12”	36”	940 lbs	761-5S	761-5A	761-7S	761-7A	6230R
12”	42”	500 lbs	661Y5S	661Y5A	661Y7S	661Y7A	6250
12”	42”	900 lbs	761Y5S	761Y5A	761Y7S	761Y7A	6250R
12”	48”	430 lbs	661W5S	661W5A	661W7S	661W7A	6240
12”	48”	700 lbs	761W5S	761W5A	761W7S	761W7A	6240R
<b>18” Depth</b>							
18”	36”	700 lbs	663-5S	663-5A	663-7S	663-7A	6231
18”	36”	1,170 lbs	763-5S	763-5A	763-7S	763-7A	6231R
18”	42”	500 lbs	663Y5S	663Y5A	663Y7S	663Y7A	6251
18”	42”	900 lbs	763Y5S	763Y5A	763Y7S	763Y7A	6251R
18”	48”	440 lbs	663W5S	663W5A	663W7S	663W7A	6241
18”	48”	740 lbs	763W5S	763W5A	763W7S	763W7A	6241R
<b>24” Depth</b>							
24”	36”	721 lbs	665-5S	665-5A	665-7S	665-7A	6232
24”	36”	1,000 lbs	765-5S	765-5A	765-7S	765-7A	6232R
24”	42”	500 lbs	665Y5S	665Y5A	665Y7S	665Y7A	6252
24”	42”	900 lbs	765Y5S	765Y5A	765Y7S	765Y7A	6252R
24”	48”	450 lbs	665W5S	665W5A	665W7S	665W7A	6242
24”	48”	720 lbs	765W5S	765W5A	765W7S	765W7A	6242R
<b>36” Depth</b>							
36”	36”	670 lbs	667-5S	667-5A	667-7S	667-7A	6234
36”	36”	790 lbs	767-5S	767-5A	767-7S	767-7A	6234R

V-Grip™ Solid Shelving, Closed, 84”H

Depth	Width	Shelf Capacity	5 Shelves Starter	5 Shelves Add-On	7 Shelves Starter	7 Shelves Add-On	Extra Shelf
<b>12” Depth</b>							
12”	36”	650 lbs	671-5S	671-5A	671-7S	671-7A	6230
12”	36”	940 lbs	771-5S	771-5A	771-7S	771-7A	6230R
12”	42”	500 lbs	671Y5S	671Y5A	671Y7S	671Y7A	6250
12”	42”	900 lbs	771Y5S	771Y5A	771Y7S	771Y7A	6250R
12”	48”	430 lbs	671W5S	671W5A	671W7S	671W7A	6240
12”	48”	700 lbs	771W5S	771W5A	771W7S	771W7A	6240R
<b>18” Depth</b>							
18”	36”	700 lbs	673-5S	673-5A	673-7S	673-7A	6231
18”	36”	1,170 lbs	773-5S	773-5A	773-7S	773-7A	6231R
18”	42”	500 lbs	673Y5S	673Y5A	673Y7S	673Y7A	6251
18”	42”	900 lbs	773Y5S	773Y5A	773Y7S	773Y7A	6251R
18”	48”	440 lbs	673W5S	673W5A	673W7S	673W7A	6241
18”	48”	740 lbs	773W5S	773W5A	773W7S	773W7A	6241R
<b>24” Depth</b>							
24”	36”	721 lbs	675-5S	675-5A	675-7S	675-7A	6232
24”	36”	1,000 lbs	775-5S	775-5A	775-7S	775-7A	6232R
24”	42”	500 lbs	675Y5S	675Y5A	675Y7S	675Y7A	6252
24”	42”	900 lbs	775Y5S	775Y5A	775Y7S	775Y7A	6252R
24”	48”	450 lbs	675W5S	675W5A	675W7S	675W7A	6242
24”	48”	720 lbs	775W5S	775W5A	775W7S	775W7A	6242R
<b>36” Depth</b>							
36”	36”	670 lbs	677-5S	677-5A	677-7S	677-7A	6234
36”	36”	790 lbs	777-5S	777-5A	777-7S	777-7A	6234R



ONE DECISION • INFINITE SOLUTIONS

SMALL BUSINESS




MADE IN USA

**V-Grip™ Shelving features the most efficient fastening principle known:**


Corner shelf reinforcements with extruded studs insert easily into tapered slots in uprights. Shelf corner drops firmly over corner reinforcement and seats itself. Four-way, crossed tension minimizes deflection, and imparts superior strength and rigidity to the unit.



Double-flanged V-Grip uprights allow easy side-by-side assembly of shelving in rows, with the strongest configuration. Each flange of the upright supports a shelf from one adjoining unit only.



Heavy duty V-Grip shelves are constructed of 18-gauge steel, and double-flanged on all four sides for maximum strength and firmness.




Common upright clamp provides back-to-back reinforcement.\*\*



Optional drawers maximize cubic density in V-Grip shelving.

**Versatile V-Grip uprights**

Permit practical back-to-back assembly of shelving units, with the same, strong reinforcement that actually strengthens shelves and uprights, yet permits their easy adjustment, and features a capacity up to 9000 lbs.



Shelves adjust instantly on 1 1/2" centers, without disturbing shelves in adjoining units.

Corner reinforcement inserts into upright; shelf simply fits down over it, and locks into place.\*

Tapered slots in uprights accept corner reinforcements for 4-way shelf support.

Double-flanged upright avoids two shelves from adjoining units placing stress on a single flange.

\* Shown in color for clarity, actual part is zinc plated.

\*\* Shown in color for clarity, actual part is galvanized steel.

A standard color chart is available at the beginning of each section with a more detailed one on page 141.