

Charging Cart / Charging & Management Cart



ONE cart fits all!

Chromebooks • Tablets • Laptops

The latest in device charging technology, the Ergotron Zip40 Charging Cart, offers versatility and flexibility with the ultimate cart agility. Because it supports up to 40 devices and is fully safety certified, it's a smart choice for education, healthcare and enterprise environments. Its small footprint and rugged steel construction handles rigorous use and demanding conditions.

Featuring Ergotron's PowerShuttle® power management technology, the system efficiently charges up to **30% faster** than a standard round-robin system. With just one power cord plugged into a standard wall outlet, it safely prevents overloading of electrical circuits by automatically determining the maximum number of devices that can be charged at one time.



MORE CAPACITY

- Charges up to 40 tablet, Chromebook™, Ultrabook, MacBook® and laptop devices with a 15.6" (or smaller) screen size

MORE AGILITY

- Zip40 dual-wheel, 5" casters create a super smooth ride over a variety of flooring surfaces
- Cube-like, compact shape makes it easy to zip through tight spaces




The Zip40 Charging Cart uses dual-wheel, 5" casters that require 33% less push/pull force than carts with single-wheel casters

MORE EFFICIENCY

- PowerShuttle technology efficiently charges up to 30% faster with a single power cord plugged into a standard wall outlet

Faster Charge



- Safely prevents overloading of electrical circuits by automatically determining the maximum number of devices that can be charged at one time
- Includes a convenient ON/OFF power button
- Removeable, locking rear-access door to the adapter storage area allows for easy, one-time setup and clean cable management
- Well-designed ventilation and continuous operating fans keep devices cool
- Ships fully assembled

MORE SECURITY

- Rugged steel construction handles rigorous use and demanding conditions
- Durable steel doors include 3-point locking mechanism with separate key lock
- Add padlock for additional door security
- Optional security bracket kit locks cart to floor or wall



SUPER SAFE

- For user and equipment safety, the entire cart is tested and certified to UL 60950



MORE FLEXIBILITY

- Adjustable dividers let you customize capacity:
 - Standard 1.1"-wide (28 mm) slots accommodate up to 40 devices, plus a partial shelf for extra storage
 - Adjust slots to 1.9" (48 mm) to accommodate up to 30 laptops or thicker devices with large cases
- Mix and match devices; move and remove dividers
- Includes external auxiliary outlet to power peripherals
- Ethernet management capability also available – carts are upgradable
- Location included for installation of a Wireless Access Point (WAP not included)

(continued on back)

Zip40

Charging Carts with Ethernet Management Capability

- “Charge only” carts can easily be upgraded to management capability in the future as technology needs change
- Easy to update devices via Wake-On-LAN
- Pre-installed CAT6 Ethernet cables and mounting brackets for a customer-provided 1U standard rack mountable Ethernet switch (switch not included)

Maximum dimensions of switch:

17.5" W x 12.4" D x 1.8" H (44 x 26 x 4,4 cm)

Maximum weight of the switch: 12 lbs (5,4 kg)



Durable steel doors include a 3-point locking mechanism with separate key lock; padlock can be added for even more door security



Separate rear-access door to the adapter storage area is easily removed for one-time set-up and clean cable management

Custom country-specific outlet strips include plenty of space to fit oversized wall plug or brick-style AC adapters

External Auxiliary Outlet(s) give you an 'always-on' outlet to plug in extra peripherals, such as a printer or document camera. No need to choose between using the auxiliary outlets and charging devices – use both at the same time!

CERTIFICATION
UL 60950 Safety of Information Technology Equipment, CAN/CSA C22 2 No. 60950
UL 1678 Household, Commercial and Institutional-Use Carts, Stands, and Entertainment Centers for Use with Audio and/or Video Equipment
ICES-003 Issue 4, Class A
FCC Part 15 Class A
Country-specific certification as required
RoHS and Reach compliant material used

Charge. Secure. Protect. Transport.

Chromebooks • Tablets • Laptops



Zip40 Charging Cart Zip40 Charging and Management Cart

Part Number (black & silver)	Charging Only US/CA/MX DM40-1009-1 EU DM40-1009-2 UK/IE/SG/MY/HK DM40-1009-3 AU/NZ DM40-1009-4 CN DM40-1009-5 JP DM40-1009-6	Charging and Management US/CA/MX DM40-1008-1 EU DM40-1008-2 UK/IE/SG/MY/HK DM40-1008-3 AU/NZ DM40-1008-4 CN DM40-1008-5 JP DM40-1008-6
Compatible Devices	Tablets, Chromebook, Ultrabook, MacBook and laptop devices with ≤ 15.6" LCD size with dimensions up to maximum 17.1"W x 11.2" H (43,4 x 28,4 cm) including case and power cord plug (Verify device dimensions for compatibility)	
Product Includes	Charging Carts: 40 dividers, 9 small device divider stoppers, four 10-outlet power strips, two 20-unit brick storage trays, four 5" dual-wheel locking casters, external auxiliary outlet(s), two mounting brackets for Ethernet switch, two internal auxiliary outlets for Ethernet switch and WAP installation, power ON/OFF switch, 2 keys, and country-specific power cord 12.5' long (3.8 m) stored in a recessed cord wrap Charging and Management Carts: Includes Charging Cart components above plus: 40 CAT6 Ethernet cables, three Ethernet cable storage trays, one 19" (5,9 m) CAT6 Ethernet cable and Velcro cable management strips	
AC Charge	Custom country-specific outlet strips include plenty of space to fit oversized wall plug or brick-style AC adapters; use adapters that come with devices	
Auxiliary Outlet(s)	2 external receptacles – US/CA/MX, JP 1 external receptacle – EU, UK/IE/SG/MY/HK, AU, CN	
Screen Size	≤ 15.6"	
# of Devices	Up to 40 with 1.1"-wide (28 mm) slots; up to 30 with 1.9"-wide (48 mm) slots	
Slot Size	17.1"W x 11.2" H (43,4 x 28,4 cm)	
UL Certification	Full UL 60950 and UL 1678 certification	
Security	3-point locking steel doors with key lock	
Power System	US/CA/MX/JP: 100-120V~, 12-10A, 50/60 Hz EU/UK/IE/CN/SG/MY/HK/AU/NZ: 220-240V~, 12-10A, 50/60 Hz	
Maximum WAP Dimensions	10"W x 10"D x 2.2"H (25,4 x 25,4 x 5,6 cm)	
Weight Capacity	TOTAL: 255 lbs (116 kg) 76.5 lbs (34,7 kg) per shelf; 25 lbs (11,3 kg) top surface	
Product Dimensions	30.3"W x 45.4"H x 26.1"D (77 x 115 x 66 cm)	
Cart Weight (without devices)	Zip40 Charging and Management Cart: 181 lb (82 kg) Zip40 Charging Cart: 175 lb (79 kg)	
Shipping Dimensions	37"W x 30"D x 52"H (94 x 76 x 132 cm)	
Shipping Weight	Zip40 Charging and Management Cart: 227 lb (103 kg) Zip40 Charging Cart: 221 lb (100 kg)	
Warranty	Lifetime mechanical, 3 years electrical, 1 year cables (power and Ethernet)	

© 2016 Ergotron, Inc. rev. 02/24/2016/EA Literature made in US
Content is subject to change without notification

Americas Sales and Corporate Headquarters

St. Paul, MN USA
(800) 888-8458
+1-651-681-7600
www.ergotron.com
sales@ergotron.com

EMEA Sales

Amersfoort, The Netherlands
+31 33 45 45 600
www.ergotron.com
info.eu@ergotron.com

APAC Sales

Tokyo, Japan
www.ergotron.com
apaccustomerservice@ergotron.com

Worldwide OEM Sales

www.ergotron.com
info.oem@ergotron.com

ERGOTRON®