PRODUCT SPECIFICATIONS



20' Contractor Web SRL

7276WR

Features

- · 20' working length.
- Dyneema web has high strength and resistance to abrasion and higher temperatures.
- Reduces arrest forces to less than 900 lbs in overhead applications.
- Lightweight nylon and glass housing with independent steel frame.

Material Specifications

Webbing: Dyneema; Min. 4,000 lbs. tensile strength

Connectors: Alloy Steel; Min. 5,000 lbs. tensile strength

Connector Gates: Alloy Steel; Min. 220 lbs. front load and

350 lbs. side load

Performance Specifications

Tensile Strength: Min. 3,000 lbs.

Max. Capacity: 310 lbs. Max. Freefall: 2 feet

Average Arrest Force: Less than 900 lbs.

Max. Elongation: 42 inches

Relevant Standards

OSHA: *CFR1926.502, CFR1910.66*

ANSI: A10.32-2004

Z359.1-2007

Warnings

- · Read, understand and follow all labels and instructions prior to use.
- · Inspect before each use.
- · Remove from service if there is evidence of damage or excessive wear.
- · Remove from service if there is any signs of activation.
- · For use in overhead applications maximum allowable freefall = 2 feet!



FallTech 1306 S. Alameda St. Compton, CA 90221 Tele: 323-752-0066 www.falltech.com