

PRODUCT SPECIFICATIONS

WireForm Anchor

#7407

Features

- Heavy-duty stainless-steel construction.
- Can be used repeatedly.
- Fits rated structural members up to 5" in diameter.
- Intended only for overhead applications.
- Meets the requirements of OSHA 1926 and ANSI Z359.

Material Specifications

Wire: *SAE 304 Stainless Steel*
Formed Eye: *Alloy Steel; Min. 5,000 lbs. tensile strength*

Performance Specifications

Tensile Strength: *Min. 5,000 lbs.*
Max. Capacity: *425 lbs.*

Relevant Standards

OSHA: *CFR1926.502, CFR1910.66*
ANSI: *A10.32-2004, Z359.1-2007*

Warnings

- Read, understand and follow all labels and instructions prior to use.
- Inspect before each use.
- Remove from service if there is evidence of damage or excessive wear.



Warning: *Only use on overhead, horizontal members. Do not attach to vertical or diagonal members, and do not use if there is any possibility that the anchor may slide off of the member to which it has been attached.*

FallTech 1306 S. Alameda St. Compton, CA 90221 Tele: 323-752-0066 www.falltech.com