

PRODUCT SPECIFICATIONS

Reusable Roof Anchor

#7410

Features

- Heavy-duty alloy-steel construction.
- Can be used repeatedly.
- Holes marked for use with either nails or screws.
- Counter-sunk screw holes.
- Conforms to roof peaks from 0 - 12/12.
- Rated at over 5,000 lbs..
- Meets the requirements of OSHA 1926 and ANSI Z359.

Material Specifications

- Wing Plates:** *SAE 1008 steel*
- D-Rings:** *Alloy Steel; Min. 5,000 lbs. tensile strength*

Performance Specifications

- Tensile Strength:** *Min. 5,000 lbs.*
- Max. Capacity:** *425 lbs.*

Relevant Standards

- OSHA:** *CFR1926.502, CFR1910.66*
- ANSI:** *A10.32-2004, Z359.1-2007*

Warnings

- Read, understand and follow all labels and instructions prior to use.
- Inspect before each use.
- Remove from service if there is evidence of damage or excessive wear.



FallTech 1306 S. Alameda St. Compton, CA 90221 Tele: 323-752-0066 www.falltech.com

WARNING: THIS SPECIFICATION SHEET PROVIDES AN OVERVIEW OF PRODUCTS AVAILABLE FROM FALLTECH. CARE HAS BEEN TAKEN TO ASSURE THE ACCURACY OF THE INFORMATION. IT DOES NOT PROVIDE IMPORTANT PRODUCT WARNINGS AND INSTRUCTIONS. FALLTECH RECOMMENDS ALL USERS OF FALL PROTECTION EQUIPMENT UNDERGO THOROUGH TRAINING, AND THAT ALL WARNINGS AND INSTRUCTIONS PROVIDED WITH THESE PRODUCTS BE THOROUGHLY READ UNDERSTOOD PRIOR TO USE. FAILURE TO READ AND FOLLOW ALL PRODUCT WARNINGS AND INSTRUCTIONS COULD RESULT IN SERIOUS INJURY OR DEATH.