

PRODUCT SPECIFICATIONS

6' Cable PassThru Anchor Sling

7428

Features

- 1/4" Vinyl-coated galvanized steel cable has high strength and is nearly impervious to cuts and abrasion.
- Rugged forged alloy-steel hardware allows for easy pass-through installation.
- Ideal for I-beams and other properly rated structural members, particularly in harsh environments.
- Economical: Can be used repeatedly.
- Meets the requirements of OSHA 1926 and ANSI Z359.

Material Specifications

- Cable:** *1/4" Vinyl Coated Galvanized;
Min. 5,000 lbs. tensile strength*
- D-Rings:** *Alloy Steel; Min. 5,000 lbs. tensile strength*

Performance Specifications

- Tensile Strength:** *Min. 5,000 lbs.*
- Max. Capacity:** *425 lbs.*

Relevant Standards

- OSHA:** *CFR1926.502, CFR1910.66*
- ANSI:** *A10.32-2004, Z359.1-2007*

Warnings

- Read, understand and follow all labels and instructions prior to use.
- Inspect before each use.
- Remove from service if there is evidence of damage or excessive wear.



FallTech 1306 S. Alameda St. Compton, CA 90221 Tele: 323-752-0066 www.falltech.com

WARNING: THIS SPECIFICATION SHEET PROVIDES AN OVERVIEW OF PRODUCTS AVAILABLE FROM FALLTECH. CARE HAS BEEN TAKEN TO ASSURE THE ACCURACY OF THE INFORMATION. IT DOES NOT PROVIDE IMPORTANT PRODUCT WARNINGS AND INSTRUCTIONS. FALLTECH RECOMMENDS ALL USERS OF FALL PROTECTION EQUIPMENT UNDERGO THOROUGH TRAINING, AND THAT ALL WARNINGS AND INSTRUCTIONS PROVIDED WITH THESE PRODUCTS BE THOROUGHLY READ UNDERSTOOD PRIOR TO USE. FAILURE TO READ AND FOLLOW ALL PRODUCT WARNINGS AND INSTRUCTIONS COULD RESULT IN SERIOUS INJURY OR DEATH.