




CANCUN™

**FP80120B
52" Wet
Location Fan**



	A	B
Fan w/4.5" downrod	13.91"	12.95"
Fan w/12" downrod	21.41"	20.45"
Fan w/18" downrod	27.41"	26.45"
Fan w/24" downrod	33.41"	32.45"
Fan w/36" downrod	45.41"	44.45"
Fan w/48" downrod	57.41"	56.45"
Fan w/60" downrod	69.41"	68.45"
Fan w/72" downrod	81.41"	80.45"

Available Finish	
OB	Oil-Rubbed Bronze

INSTALLATION REQUIREMENTS:

Ceiling fan attaches to electrical junction box securely anchored and capable of withstanding a load of at least 50 lbs.

ELECTRICAL REQUIREMENTS:

Ceiling fan requires a grounded electrical supply line of 120 volts AC, 60 Hz, 15 amp circuit.

MOTOR SPECS:

188 x 25 motor is designed for optimal performance with this fan. Fan is Energy Star Rated.

BLADE SETS:

A set of five 22" wet location rated all-weather antique woven bamboo finish blades is included.

CONTROL OPTIONS:

Optional CW1, CW1SW, CW2, CW5 and CWRL4 wall controls and CRL4WH and CRL8TS remote controls (with receiver units) are available—sold separately. Instructions are provided with each control.

LIGHTING OPTIONS:

Optional lighting fitters and light kits are available. See our catalog or visit www.fanimation.com for lighting options.

DOWNROD OPTIONS:

The Cancun™ fan comes with a 1" Dia. x 4.5" downrod. Optional downrods are available in 12", 18", 24", 36", 48", 60", and 72". For installations requiring a longer downrod, a downrod coupler is available. The Cancun™ fan can be mounted on a sloped ceiling up to 30°. Most sloped ceiling installations require a downrod longer than the standard 6" downrod. Optional sloped ceiling ball kits (SCB1-52) are available for up to 52°. Optional close-to-ceiling kit is available as well-sold separately. Call your local dealer for more information.

LOCATION USE:

Fan is rated for dry, damp and wet locations.

Airflow / Energy Efficiency Info (120V)					
Fan Speed	Max RPM	CFM	CFM / Watts	Amps	Watts
High	148	5715	82	0.59	70.0
Med	101	3815	114	0.41	33.5
Low	50	1863	190	0.22	9.8