



Home Comfort

FFPH1222R1

Portable Air Conditioner/Heater



Product Dimensions

Height	30-1/8"
Width	18-5/16"
Depth	15-5/8"

More Easy-To-Use Features

Remote Control

Allows you to precisely control the temperature and fan speed from across the room.

Effortless™ Clean Filter

Our antibacterial filter reduces bacteria, room odors and other airborne particles for a cool, comfortable environment.

Multi-Speed Fan

Features three different fan speeds, for more cooling flexibility.

Sleep Mode

Quiet operation keeps you cool without keeping you awake. Plus, Sleep Mode gradually increases room temperature after being activated.

Quickly Cools

Quickly cool a room on hot days.

Comfort Control Design

Easily control the direction of your cool air, wherever your unit is.

Effortless™ Restart

Automatically resumes operating at its previous settings when power is restored to your unit.

Clean Filter Alert

Notifies you when your filter needs to be cleaned.

Power Cord

Comes with an extra long three-prong cord that makes extension cords unnecessary.

24-Hour On/Off Timer

Keep things cool on your schedule.

Signature Features

Ready-Select® Controls

Easily select options with the touch of a button.

Supplemental Heating Option

Our versatile unit offers a supplemental heating capability, providing you with an additional heat source when needed.

SpaceWise® Portable Design

Wheels allow you to easily move the air conditioner from room to room, providing cool air when and where you need.

Effortless™ Temperature Control

Our air conditioners maintain the preset room temperature, so you will remain comfortable at all times.


Performance	BTUs
Cool	12,000
Heat	4,100

Performance	
BTU (Cool)	12,000
BTU (Heat)	4,100
Dehumidification (Pints/Hour)	3.1
Cool Area (Up To Sq.Ft.)	550
Energy Efficiency Ratio	8.9
Electrical	
Volts	115
Amps (Cool)	11.8
Amps (Heat)	11.6
Watts (Cool)	1,350
Watts (Heat)	1,320
Length of Power Cord (Min./Max.)	6'/6.5'
Plug Type (NEMA)	LCDI (5-15P)
Features	
Electronic Controls	Ready-Select® Controls
Fan Speeds (Cool/Fan/Heat)	3/3/1
Low Voltage Start-Up	Yes
Auto Cool Function	Yes
Energy Save	
Sleep Mode	Yes
Filter Check	Yes
24-Hour On/Off Timer	Yes
Clean Air Ionizer	
Remote Control	Full-Function
Air CFM (High/Med/Low)	497/450/404
Air Direction Control	Swing
Fresh Air/Exhaust Vent/Closed	No/Yes/No
Filter Type	Antibacterial Mesh
Filter Access	Rear
Warranty ¹	Yes
Certifications	
Performance	ASHRAE
Specifications	
Refrigerant	R410a
Shipping Weight (Approx.)	86 Lbs.

¹Warranty 5 year sealed system/1 year full parts and labor.



Plug Type (NEMA)
5-15P



NOTE: For planning purposes only. Always consult local and national electric and plumbing codes. Refer to Product Installation Guide for detailed installation instructions on the web at frigidaire.com.



Product Dimensions	
A - Height	30-1/8"
B - Width	18-5/16"
C - Depth	15-5/8"

Accessories information available on the web at frigidaire.com