

## FFPA1222U1

### HOME COMFORT PORTABLE AIR CONDITIONER



### SIGNATURE FEATURES

#### Multi-Speed Fan

Features three different fan speeds, for more cooling flexibility.

#### Remote Control

Allows you to precisely control the temperature and fan speed from across the room.

#### Effortless™ Clean Filter

Our antibacterial filter reduces bacteria, room odors and other airborne particles for a healthier, more comfortable environment.

#### Programmable 24-Hour On/Off Timer

Customize times to fit your schedule for immediate comfort when you get home. The built-in timer allows you to preset the unit to turn on and off in half-hour increments.

### PRODUCT DIMENSIONS

Height	27-29/32"
Width	18-23/32"
Depth	15-5/32"

### MORE EASY-TO-USE FEATURES

#### Sleep Mode

Maximum comfort throughout the evening hours with the added benefit of energy savings. With Sleep Mode, the temperature gradually increases a few degrees over the evening.

#### Ready-Select® Controls

Easily select options with the touch of a button.

#### SpaceWise® Portable Design

Wheels allow you to easily move the air conditioner from room to room, providing cool air when and where you need.

#### Effortless™ Restart

Automatically resumes operating at its previous settings when power is restored to your unit.

#### Effortless™ Temperature Control

Our air conditioners maintain the preset room temperature, so you will remain comfortable at all times.

PERFORMANCE	BTUs
Cooling	12,000
D.O.E.	6,500

# FFPA1222U1 HOME COMFORT

## PORTABLE AIR CONDITIONER

FRIGIDAIRE

### PERFORMANCE

ASHRAE BTU (Cool)	10,000
D.O.E. BTU	6,500
Dehumidification (Pints/Hour)	3.3
Cool Area (Up To Sq.Ft.)	550
Energy Efficiency Ratio	10.2

### ELECTRICAL

Volts	115
Amps (Cool)	9.5
Watts (Cool)	1,150
Length of Power Cord (Min./Max.)	6'/6.5'
Plug Type (NEMA)	LCDI (5-15P)

### FEATURES

Electronic Controls	Ready-Select® Controls
Fan Speeds (Cool/Fan)	3/3
Low Voltage Start-Up	Yes
Energy Save	
Sleep Mode	Yes
Filter Check	Yes
24-Hour On/Off Timer	Yes
Clean Air Ionizer	
Remote Control	Full-Function
Air CFM (High/Med/Low)	230/212/194
Air Direction Control	Swing
Fresh Air/Exhaust Vent/Closed	No/Yes/No
Filter Type	Antibacterial Mesh
Filter Access	Rear
Warranty <sup>1</sup>	Yes

### CERTIFICATIONS

Performance	ASHRAE, D.O.E
-------------	---------------



### SPECIFICATIONS

Refrigerant	R410a
Shipping Weight (Approx.)	66 Lbs.

<sup>1</sup>Warranty 5 year sealed system/1 year full parts and labor.

### PRODUCT DIMENSIONS

A - Height	27-29/32"
B - Width	18-23/32"
C - Depth	15-5/32"



Plug Type (NEMA)  
5-15P



**Note:** For planning purposes only. Always consult local and national electric, gas and plumbing codes. Refer to Product Installation Guide for detailed installation instructions on the web at [frigidaire.com](http://frigidaire.com).

Specifications subject to change. Accessories information available on the web at [frigidaire.com](http://frigidaire.com)

FRIGIDAIRE

USA • 10200 David Taylor Drive • Charlotte, NC 28262 • 1-800-FRIGIDAIRE • [frigidaire.com](http://frigidaire.com)  
CANADA • 5855 Terry Fox Way • Mississauga, ON L5V 3E4 • 1-800-265-8352 • [frigidaire.ca](http://frigidaire.ca)

FFPA1222U1 01/18  
© 2018 Electrolux Home Products, Inc.