

FFRA2822U2



SIGNATURE FEATURES

Energy Saver Mode

Reduce utility bills by allowing the unit to turn on and off at different intervals to ensure the room temperature stays at the set temperature.

Sleep Mode

Maximum comfort throughout the evening hours with the added benefit of energy savings. With Sleep Mode, the temperature gradually increases a few degrees over the evening.

Multi-Speed Fan

Features three different fan speeds, for more cooling flexibility.

Programmable 24-Hour On/Off Timer

Customize times to fit your schedule for immediate comfort when you get home. The built-in timer allows you to preset the unit to turn on and off in half-hour increments.

HOME COMFORT

HEAVY-DUTY AIR CONDITIONER

PRODUCT DIMENSIONS

Height	18-5/8"
Width	26-17/32"
Depth	26-5/16"

MORE EASY-TO-USE FEATURES

Effortless™ Temperature Control

Our air conditioners maintain the preset room temperature, so you will remain comfortable at all times.

Effortless™ Remote Temperature Control

A thermostat located on your air conditioner's remote control precisely maintains preset room temperature, so you will remain comfortable at all times.

Remote Control

Allows you to precisely control the temperature and fan speed from across the room.

Easier Installation

With the slide-out chassis, you have an easier solution to installing your air conditioner. First install the outer cabinet of the AC in the window, then slide the interior of the air conditioner into place.

Effortless™ Clean Filter

Our antibacterial filter reduces bacteria, room odors and other airborne particles for a healthier, more comfortable environment.

SpaceWise® Adjustable Side Panels

The Adjustable Side Panels will extend to best fit your window.

Power Cord

Comes with an extra long three-prong cord — makes extension cords unnecessary.

PERFORMANCE	BTUS
Cool	28,300/28,000

FFRA2822U2 HOME COMFORT

FRIGIDAIRE

HEAVY-DUTY AIR CONDITIONER

PERFORMANCE

BTU (Cool)	28,300/28,000
Dehumidification (Pints/Hour)	8.1
Cool Area (Up To Sq.Ft.)	1,900
Combined Energy Efficiency Ratio	9.0
Energy Efficiency Ratio	9.0

ELECTRICAL

Volts	230V/208V
Amps (Cool)	13.9/15.2
Watts (Cool)	3,100/3,100
Length of Power Cord (Min./Max.)	5'/6'
Plug Type (NEMA)	LCDI (6-30P)

FEATURES

Electronic Controls	Ready-Select® Controls
Fan Speeds (Cool/Fan)	3/3
Low Voltage Start-Up	Yes
Auto Cool Function	Yes
Energy Saver Mode	Yes
Sleep Mode	Yes
Filter Check	Yes
24-Hour On/Off Timer	Yes
Clean Air Ionizer	
Remote Control	Full-Function/Remote Thermostat
Air CFM (High/Med/Low)	495/453/412
Air Direction Control	6-Way
Fresh Air/Exhaust Vent/Closed	No/No/Yes
Filter Type	Antibacterial Mesh
Filter Access	Tilt-Out
Slide-Out Chassis	Yes
Window Mounting Kit (Included)	Pleated Quick Mount
Warranty ¹	Yes


CERTIFICATIONS

Performance	AHAM
-------------	------

SPECIFICATIONS

Refrigerant	R410a
Shipping Weight (Approx.)	159 Lbs.

¹Warranty 5 year sealed system/1 year full parts and labor.



Plug Type (NEMA)
6-30P

PRODUCT DIMENSIONS


A - Height	18-5/8"
B - Width	26-17/32"
C - Depth	26-5/16"

WINDOW DIMENSIONS

D - Height (Min.)	19-1/4"
E - Width (Min./Max.)	30" / 41"

WALL CUTOUT DIMENSIONS

F - Max. Wall Thickness	8-1/4"
Height	18-29/32"
Width	26-3/4"



Note: For planning purposes only. Always consult local and national electric, gas and plumbing codes. Refer to Product Installation Guide for detailed installation instructions on the web at frigidair.com.

Specifications subject to change. Accessories information available on the web at frigidair.com

FRIGIDAIRE

USA • 10200 David Taylor Drive • Charlotte, NC 28262 • 1-800-FRIGIDAIRE • frigidair.com
CANADA • 5855 Terry Fox Way • Mississauga, ON L5V 3E4 • 1-800-265-8352 • frigidair.ca

FFRA2822U2 01/18

© 2018 Electrolux Home Products, Inc.