

FFRE1233U1

HOME COMFORT

COMPACT AIR CONDITIONER



SIGNATURE FEATURES

Effortless™ Remote Temperature Control

Remote control thermostat precisely maintains preset room temperature, so you can remain comfortable at all times.

Programmable 24-Hour On/Off Timer

With the 24-Hour On/Off Timer, you can ensure your home will be cool and comfortable when you want it to be without having to worry about running up your utility bills. The built-in timer allows you to preset the unit to turn on and off in half-hour increments.

Energy Saver Mode

Reduce your utility bills in this mode. It cools similarly to central air, with the unit turning on and off at different intervals to ensure the room temperature stays at the set temperature.

Multi-Speed Fan

Features three different fan speeds, for more cooling flexibility.

PRODUCT DIMENSIONS

Height	15-3/4"
Width	21-11/32"
Depth	21-1/4"

MORE EASY-TO-USE FEATURES

Sleep Mode

With Sleep Mode, the temperature gradually increases a few degrees over the evening, saving energy and creating a comfortable environment during the evening hours.

Remote Control

Offers you the flexibility to control the temperature and fan speed from anywhere in the room.

Effortless™ Clean Filter

Our antibacterial filter reduces bacteria, room odors and other airborne particles for a healthier, more comfortable environment.

SpaceWise® Adjustable Side Panels

The Adjustable Side Panels will extend to best fit your window.

Power Cord

Comes with an extra long three-prong cord — makes extension cords unnecessary.

Effortless™ Restart

Automatically resumes operating at its previous settings when power is restored to your unit.

Clean Filter Alert

Alert notifies you when your filter needs to be cleaned so you don't have to keep track of it yourself.

CERTIFICATIONS

ENERGY STAR®



PERFORMANCE	BTUS
Cool	12,100

FFRE1233U1 HOME COMFORT

COMPACT AIR CONDITIONER

FRIGIDAIRE

PERFORMANCE

BTU (Cool)	12,100
Dehumidification (Pints/Hour)	3.4
Cool Area (Up To Sq.Ft.)	550
Combined Energy Efficiency Ratio	12.0
Energy Efficiency Ratio	12.1

ELECTRICAL

Volts	115
Amps (Cool)	9.2
Watts (Cool)	1,000
Length of Power Cord (Min./Max.)	6' / 6.5'
Plug Type (NEMA)	LCDI (5-15P)

FEATURES

Electronic Controls	Ready-Select® Controls
Fan Speeds (Cool/Fan)	3/3
Low Voltage Start-Up	Yes
Auto Cool Function	Yes
Energy Saver Mode	Yes
Sleep Mode	Yes
Filter Check	Yes
24-Hour On/Off Timer	Yes
Clean Air Ionizer	
Remote Control	Full-Function/Remote Thermostat
Air CFM (High/Med/Low)	280/260/240
Air Direction Control	6-Way
Fresh Air/Exhaust Vent/Closed	No/No/Yes
Filter Type	Antibacterial Mesh
Filter Access	Tilt-Out
Slide-Out Chassis	
Window Mounting Kit (Included)	Pleated Quick Mount
Warranty ¹	Yes


CERTIFICATIONS

ENERGY STAR®	Yes
Performance	AHAM

SPECIFICATIONS

Refrigerant	R410a
Shipping Weight (Approx.)	79 Lbs.

¹Warranty 5 year sealed system/1 year full parts and labor.




Plug Type (NEMA)
5-15P

PRODUCT DIMENSIONS

A - Height	15-3/4"
B - Width	21-11/32"
C - Depth	21-1/4"

WINDOW DIMENSIONS

D - Height (Min.)	18-1/6"
E - Width (Min./Max.)	24" / 40"



Note: For planning purposes only. Always consult local and national electric, gas and plumbing codes. Refer to Product Installation Guide for detailed installation instructions on the web at frigidaire.com.

Specifications subject to change. Accessories information available on the web at frigidaire.com

FRIGIDAIRE

USA • 10200 David Taylor Drive • Charlotte, NC 28262 • 1-800-FRIGIDAIRE • frigidaire.com
CANADA • 5855 Terry Fox Way • Mississauga, ON L5V 3E4 • 1-800-265-8352 • frigidaire.ca

FFRE1233U1 01/18
© 2018 Electrolux Home Products, Inc.