



PLASTIC HOLLOW WALL ANCHORS			
Part Number	Screw Size	Acceptable Range of Length	Drill Size
08PA	6-8	3/4" - 1"	3/16
12PA	8-10	1" - 1 1/4"	1/4
16PA	10-12-14	1 5/32" - 1 1/2"	5/16

For best results, the screw should be 1/8 to 1/4" longer than the length of the anchor.

<b>Description</b>	An injection-molded anchor with a ribbed shank which resists "backing-out" after installation and longitudinal slits along the shaft which allows the anchor to expand when a screw is inserted.
<b>Applications/Advantages</b>	Plastic anchors are a more economical, light-duty part than steel hollow wall anchors. They can be used in sheetrock, plaster, brickwork, concrete or tile. The design of the collar allows plastic anchors to also be used in hollow materials. For use with self-tapping or wood screws.
<b>Material</b>	Polyvinylchloride or Polyethylene plastic
<b>Pullout Values*</b>	50 lbs.
<b>Color</b>	Plastic anchors are usually, but not exclusively, supplied in white.

\*Recommended safe working load is one-fourth of the proof test load.