


CENTERLINE SHELVES



The Kendall Howard Vented Centerline Shelf is one of the strongest, most stable shelves on the market. Unlike most center mount shelves which may teeter, the Kendall Howard Centerline shelf is rock solid! The heavy-gauge steel construction and welded mounting flanges give this shelf unprecedented stability and strength.

FEATURES

Center Mount Style - When mounting equipment in a 2-post rack, weight distribution is always a concern. The centerline shelf provides a 24" depth surface that evenly distributes the weight across each side of the rack.

Easy to Install - 19" EIA mounting flanges easily mount to any 19" two-post relay rack with rack screws and cage nuts.

Heavy Duty - This 24" center mount shelf can support up to 350 lbs., perfect for heavy equipment such as CPU's, servers, battery back up's, UPS's, and more.

Rounded Corners - It may be a small detail, but at Kendall Howard we think it's important. It is for that reason that all corners and edges of the centerline shelf are rounded for safe handling.

Optional Ventilation - The fully vented shelf base allows for maximum airflow to prevent valuable equipment from overheating.

SPECIFICATIONS

Style	Part Number	Width	Depth	Height	Material(s)	Finish/Color	UPC	Warranty	Shipping Method
Solid	1907-3-001-03	19"	24"	5.22"	CRS (Cold Rolled Steel)	Black Powder Coat Finish	879447000290	Limited Lifetime Warranty	FedEx Ground
Vented	1907-3-000-03	19"	24"	5.22"	CRS (Cold Rolled Steel)	Black Powder Coat Finish	879447000283	Limited Lifetime Warranty	FedEx Ground