



NON-THREADED FAN HOUSING MOUNT

NOTE:

1. FAN TYPE: TUBE AXIAL
2. VOLTAGE RATED: 115 VAC, 0.20 A
3. AIRFLOW: 66/78 CFM
4. TERMINATION: 2 TERMINALS /NO GND

UNLESS OTHERWISE SPECIFIED:
 DIMENSIONS ARE IN INCHES
 TOLERANCES:
 FRACTIONAL ± 1/8
 ANGULAR: BEND ± 1 DEGREE
 TWO PLACE DECIMAL ± .03
 THREE PLACE DECIMAL ± .01

Surface Area	
MATERIAL	
FINISH	
APPLICATION	DO NOT SCALE DRAWING

WEB PRINT	
NEXT ASSY	USED ON
APPLICATION	

PROPRIETARY AND CONFIDENTIAL
 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF KENDALL HOWARD. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF KENDALL HOWARD IS STRICTLY PROHIBITED.

	NAME	DATE
DRAWN		
CHECKED		
ENG APPR.		
MFG APPR.		
Q.A.		
COMMENTS:		

KENDALL HOWARD

TITLE:
FAN ASSEMBLY KIT

SIZE	DWG. NO.	REV
A	1908-3-001-01 WP	-
SCALE: 1:3	WEIGHT:	SHEET 2 OF 2