

## 41U KNOCKDOWN 4-POST OPEN FRAME RACK



- Fully adjustable rails from 3" to 36"
- Levelers included
- Assembles in less than 30 minutes
- Cage nut style rails
- 2,000 lb. weight capacity (Holds 1,000 lbs. on casters)
- 19" EIA 310-D compliant
- Made in the USA
- Limited Lifetime Warranty

Kendall Howard manufactures the 41U Knockdown 4-Post Open Frame Rack – one of the strongest adjustable open frame knockdown racks on the market today. Our unique, heavy duty, square tube steel design assembles with just a few bolts and makes this racking system affordable, versatile, and easy to ship. Its knockdown design makes the rack capable of shipping in a small wooden crate and ship out as a small package that can be delivered the next day. For a reliable and convenient racking solution, the 41U Knockdown 4-Post Open Frame Rack is a great option.

### FEATURES

**Mount More Rails** - Most 4-post racks allow for only two sets of vertical rails to be mounted to the rack. With our design, you can add a third set of rails and mount equipment that has different mounting depths in the same rack.

**Ships in Knockdown Position** - The rack's knockdown design allows us to ship the product as a small package keeping our shipping costs low and allowing the package to ship to almost anywhere in the world next day.

**Easy to Install** - Levelers are included to make installation quick and easy. To make the unit mobile, casters are available and can be installed onto the open frame rack.

Part Number	1940-3-001-41	UPC	879447000818
Width	23.4"	Color	Black Powder Coat Finish
Depth	36.2"	Warranty	Limited Lifetime Warranty
Height	74.9"	Shipping Method	FedEx Ground