

PERFORMANCE SERIES® LAN STATIONS/WORKBENCHES: 300 SERIES

AMERICAN
MADE 



The Kendall Howard Performance 300 Series® LAN Stations/Workbenches have a 28" deep lower shelf providing plenty of depth for storage under the work surface. Two 14" deep modular shelves form the lower shelf and together have a weight capacity of 500 lbs., making this LAN Station both strong and functional. The work surface height is fixed at 30". Another feature is the built-in cable management channel keeps network cables and power cords neat and organized. Its completely modular design makes it simple to create the perfect work station. Simply add the accessories needed to create the work station suitable for you. The Performance Series® LAN Stations/Workbenches are available in five stunning finishes: Folkstone, Hard Rock Maple, Caramel Apple, Serene Cherry, and African Mahogany.

- *Shown with optional casters (not included)
- Completely modular design
- Universal preset accessory mounting holes
- Assembles in less than 30 minutes
- Includes one full bottom shelf
- Available in five stunning finishes
- 1,000 lb. weight capacity
- Made in the USA
- Limited Lifetime Warranty

FEATURES

Multi-Functional - The 300 Series LAN Stations/Workbenches are commonly used as technology benches, video editing stations, command consoles, security monitoring stations, and much more.

Various Sizes Available - We know areas, such as shipping stations, home offices, and technology centers, vary in size and need. That's why we offer the 300 series in four sizes (24"/48"/72"/96") so you can choose the LAN station suitable for you.

Optional Accessories - Available accessories include Accessory Bars, LCD Monitor Mounts, Power Strips, Keyboard Trays, Casters, and much more. The preset mounting holes under the work surface allow for one accessory every 24". Accessories that mount above the work surface easily attach to the accessory bar.

PERFORMANCE SERIES® LAN STATIONS/WORKBENCHES SPECIFICATIONS - 300 SERIES



24"
HARD ROCK MAPLE



48"
CAMEL APPLE



72"
SERENE CHERRY



96"
AFRICAN MAHOGANY

COLOR/FINISH	FOLKSTONE	HARD ROCK MAPLE	CAMEL APPLE	SERENE CHERRY	AFRICAN MAHOGANY
SKU	5000-3-300-24	5000-3-301-24	5000-3-302-24	5000-3-303-24	5000-3-304-24
WIDTH	24"	24"	24"	24"	24"
DEPTH	31.63"	31.63"	31.63"	31.63"	31.63"
HEIGHT	30.5"	30.5"	30.5"	30.5"	30.5"
WARRANTY	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty
SHIPPING METHOD	LTL Freight	LTL Freight	LTL Freight	LTL Freight	LTL Freight

COLOR/FINISH	FOLKSTONE	HARD ROCK MAPLE	CAMEL APPLE	SERENE CHERRY	AFRICAN MAHOGANY
SKU	5000-3-300-48	5000-3-301-48	5000-3-302-48	5000-3-303-48	5000-3-304-48
WIDTH	48"	48"	48"	48"	48"
DEPTH	31.63"	31.63"	31.63"	31.63"	31.63"
HEIGHT	30.5"	30.5"	30.5"	30.5"	30.5"
WARRANTY	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty
SHIPPING METHOD	LTL Freight	LTL Freight	LTL Freight	LTL Freight	LTL Freight

COLOR/FINISH	FOLKSTONE	HARD ROCK MAPLE	CAMEL APPLE	SERENE CHERRY	AFRICAN MAHOGANY
SKU	5000-3-300-72	5000-3-301-72	5000-3-302-72	5000-3-303-72	5000-3-304-72
WIDTH	72"	72"	72"	72"	72"
DEPTH	31.63"	31.63"	31.63"	31.63"	31.63"
HEIGHT	30.5"	30.5"	30.5"	30.5"	30.5"
WARRANTY	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty
SHIPPING METHOD	LTL Freight	LTL Freight	LTL Freight	LTL Freight	LTL Freight

COLOR/FINISH	FOLKSTONE	HARD ROCK MAPLE	CAMEL APPLE	SERENE CHERRY	AFRICAN MAHOGANY
SKU	5000-3-300-96	5000-3-301-96	5000-3-302-96	5000-3-303-96	5000-3-304-96
WIDTH	96"	96"	96"	96"	96"
DEPTH	31.63"	31.63"	31.63"	31.63"	31.63"
HEIGHT	30.5"	30.5"	30.5"	30.5"	30.5"
WARRANTY	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty
SHIPPING METHOD	LTL Freight	LTL Freight	LTL Freight	LTL Freight	LTL Freight