

Pro 5 MP Fire Extinguisher

Part number 466112

Multipurpose use

Rechargeable

UL Rated 3-A, 40-B:C



Description

Suitable for use on Class A (trash, wood & paper), Class B (liquids & gases) and Class C fires (energized electrical equipment).

The Pro 5 MP unit is fitted with a pressure gauge that provides at-a-glance status, is manufactured from lightweight aluminum and a tough metal valve assembly.

Also available:
46611201 with Metal Strap Bracket.

Features

- Easy-to-read gauge tells you fire extinguisher is charged and ready for use
- Clear instruction label using graphics to show steps required to operate extinguisher
- Easy-to-pull safety pin
- Tough impact resistant metal valve, handle & lever
- 5.5 lb. of fire extinguishing agent (Average)
- 6 year limited warranty
- UL approved wall hanger
- Coast Guard (U.S.C.G) approved when fitted with mounting bracket (not supplied)
- Powder coated cylinder for corrosion protection
- U.S.C.G. approved bracket part number 466400

At a Glance

- Model Pro 5 MP
- Multipurpose Dry Chemical
- UL listed
- UL rated 3-A, 40-B:C
- Supplied with wall hanger
- Monoammonium Phosphate
- 6 year limited warranty
- Suitable for use on most common fires

For use on the following types of fire:



Pt # 466112 - 4 pack
UPC: 0-47871-66112-0
12F - 20047871661125

Product Specification

Net agent weight (Average)	5.5 lb.
Unit weight (Average)	9.0 lb.
Diameter	4.5 inches
Height	16.31 inches
Discharge time	13-15 seconds
Discharge range	12-18 feet
Operating pressure	195 psi
Cylinder	Seamless aluminum
Valve, handle, lever	Metal
Strap Bracket	U.S.C.G approved

Packaging Options



MASTER PACK

Packaging dimensions (inches)

	Depth	Width	Height
Carton	4.75	6.0	17.0
Master Pack	13.0	17.25	9.87



Kidde Residential and Commercial Division
1016 Corporate Park Drive, Mebane, NC 27302
(800) 880-6788 www.Kidde.com