

Pro 5 CD Fire Extinguisher

Part number 466180

Electrical risks

Rechargeable

UL Rated 5-B:C



Description

Suitable for use on Class B (liquids) and Class C fires (energized electrical equipment).

The Pro 5 carbon dioxide unit is environmentally safe and ideal for protecting delicate electronic equipment as the clean agent leaves no residue. The cylinder is manufactured from aluminum and the valve assembly is metal.

Features

- Clear instruction label using graphics to show steps required to operate extinguisher
- Easy-to-pull safety pin
- Tough impact resistant metal valve, handle & lever
- 5 lb. of fire extinguishing agent (Average)
- 5 year limited warranty
- UL approved wall hanger
- Powder coated cylinder for corrosion protection

At a Glance

- Model Pro 5 CD M-4
- Carbon dioxide
- UL listed
- UL rated 5-B:C
- Supplied with wall hanger
- 5 year limited warranty
- Suitable for use on energized electrical equipment

For use on the following types of fire:



Pt # 466180 - 1 pack
UPC: 0-47871-66180-0
I2F - 20047871661804

Product Specification

Net agent weight (Average)	5 lb.
Unit weight (Average)	15.0 lb.
Diameter	5.25 inches
Height	17.0 inches
Discharge time	7-9 seconds
Discharge range	3-8 feet
Operating pressure	850 psi
Cylinder	Aluminum
Valve, handle, lever	Brass & stainless steel
Strap Bracket (not supplied)	U.S.C.G approved

Packaging Options



SHIPPED IN CARTON

Packaging dimensions (inches)

	Depth	Width	Height
Carton	5.5	8.0	17.5



Kidde Residential and Commercial Division
1016 Corporate Park Drive, Mebane, NC 27302
(800) 880-6788 www.Kidde.com