

Pro 15 CD Fire Extinguisher

Part number 466182

Electrical risks

Rechargeable

UL Rated 10-B:C



Description

Suitable for use on Class B (liquids) and Class C fires (energized electrical equipment).

The Pro 15 carbon dioxide unit is environmentally safe and ideal for protecting delicate electronic equipment as the clean agent leaves no residue. The cylinder is manufactured from aluminum and the valve assembly is metal.

Features

- Clear instruction label using graphics to show steps required to operate extinguisher
- Easy-to-pull safety pin
- Tough impact resistant metal valve, handle & lever
- 15 lb. of fire extinguishing agent (Average)
- 5 year limited warranty
- UL approved wall hanger
- Powder coated cylinder for corrosion protection

At a Glance

- Model Pro 15 CD M-4
- Carbon dioxide
- UL listed
- UL rated 10-B:C
- Supplied with wall hanger
- 5 year limited warranty
- Suitable for use on energized electrical equipment

For use on the following types of fire:



Product Specification

| | |
|------------------------------|-------------------------|
| Net agent weight (Average) | 15 lb. |
| Unit weight (Average) | 40.0 lb. |
| Diameter | 6.87 inches |
| Height | 26.0 inches |
| Discharge time | 12-14 seconds |
| Discharge range | 3-8 feet |
| Operating pressure | 850 psi |
| Cylinder | Aluminum |
| Valve, handle, lever | Brass & stainless steel |
| Strap Bracket (not supplied) | U.S.C.G approved |

Packaging Options

Pt # 466182 - 1 pack
 UPC: 0-47871-66182-4
 I2F - 20047871661828



SHIPPED IN CARTON

Packaging dimensions (inches)

| | Depth | Width | Height |
|--------|-------|-------|--------|
| Carton | 7.0 | 11.75 | 29.25 |



Kidde Residential and Commercial Division
 1016 Corporate Park Drive, Mebane, NC 27302
 (800) 880-6788 www.Kidde.com