

# Pro Plus 20 MP Fire Extinguisher

Part number 468003

Multipurpose use

Rechargeable

## UL Rated 6-A:120-B:C



For use on the following types of fire:



## Description

Suitable for use on Class A (trash, wood & paper), Class B (liquids & gases) and Class C fires (energized electrical equipment).

The Pro Plus 20 MP unit is fitted with a pressure gauge that provides at-a-glance status, cylinder is manufactured from impact resistant steel and the valve assembly is all metal.



Includes metal hanger (14260).

## At a Glance

- Model Pro Plus 20 MP
- Multipurpose Dry Chemical
- UL listed
- UL rated 6-A:120-B:C
- Supplied with wall hanger
- Monoammonium Phosphate
- 6 year limited warranty
- Suitable for use on most common fires

## Features

- Easy-to-read gauge tells you fire extinguisher is charged and ready for use
- Clear instruction label using graphics to show steps required to operate extinguisher
- Easy-to-pull safety pin
- Tough impact resistant metal valve, handle & lever
- 20 lb. of fire extinguishing agent (Average)
- 6 year limited warranty
- UL approved wall hanger
- Coast Guard (U.S.C.G) approved when fitted with mounting bracket (not supplied)
- Powder coated cylinder for corrosion protection
- U.S.C.G. approved bracket part number 18117

Pt # 468003- 1 pack  
UPC: 0-47871-68003-0  
1ZF: 20047871680034

## Product Specification

Net agent weight (Average)	20 lb.
Unit weight (Average)	31 lb.
Diameter	7.25 inches
Height	21.6 inches
Discharge time	26-28 seconds
Discharge range	16-20 feet
Operating pressure	195 psi
Cylinder	Mild steel
Valve, handle, lever	Metal
Strap Bracket (not supplied)	U.S.C.G approved

## Packaging Options



MASTER PACK



Kidde Residential and Commercial Division  
1016 Corporate Park Drive, Mebane, NC 27302  
(800) 880-6788 www.Kidde.com