

BEACON 980

Wide Area LED Tower Light

Part of the LED JOBSITE
LEDJOBSITE.COM

The LE980LED is an incredibly bright LED area light that is powerful enough to light up large construction sites. The versatile light head can be retrofitted onto virtually any base.

Ideal for large construction, military, and shutdowns, the LE980LED is durable, rugged, easily transportable and will provide the lighting power you need instantly, every time.

Replace any 1000W metal halide light with the LE980LED for a safer and smarter lighting solution in any application. The LE980LED utilizes the latest advancements in LED technology to provide a bright, uniform light in a rugged, yet compact portable design.

KEY FEATURES

- Lightweight and easily portable.
- LEDs will last over 50,000 hours.
- No bulb replacement required.
- Rated for outdoor use.
- Instant start-up, at full output, even in cold temperatures.
- Rugged heavy duty frame.

KEY BENEFITS

- Safer working environment.
- Lower total cost of ownership.
- Reduced downtime on job sites.
- Energy saving device for a greener footprint.
- Extremely versatile light for multiple applications.

INDUSTRIES/APPLICATIONS

- Construction
- Maintenance
- General contractors
- Emergency responders
- Military
- Events



LE980LED-CART
STRONG CART MOUNT (19"-12.5')



LE980LED LIGHT HEAD



LE980LED-TRW
STRONG TRIPOD MOUNT (6'-12')

SPECIFICATIONS	
VOLTAGE	120V AC • 60 Hz
WATTAGE	200W
LIGHT TEMPERATURE	4500K (bright white light • no blue tint)
LUMENS	30,000 (replaces 1000W metal halide)
LED LIGHT EXPECTANCY	High output Cree LEDs rated for over 50,000 hours
CONSTRUCTION	Cast aluminum housing, polycarbonate lenses
DIMENSIONS (light head)	Length 12.5" x Height: 17" x Depth 6" • 16 lbs
WEATHERPROOF RATING	IP65

No bulbs. No heat. Instant start-up. Bright light everywhere, every time.



For more information about our other lines of portable electrical equipment for the toughest workplaces:
www.lindequipment.net | info@lindequipment.net | T: 877.475.LIND

