



MCR
SAFETY

Prodigy

Safety Glasses

Plus Series

Specification Sheet

PRODUCT DESCRIPTION:

Strong and flexible, the Prodigy® series features two lens styles: The DLX is a two-lens frame, fitted with 58mm lenses. The SLX is a single-lens style which provides a wide field of vision and angular coverage for added protection. Constructed from a nylon formulation, the Prodigy® weighs only 1.2 ounces. Scratch-resistant polycarbonate lenses filter out 99.9 percent of UV rays. A perfect blend of style and comfort.

FEATURES:

- Exclusive Duramass® scratch-resistant coating
- Rugged polycarbonate lens filters 99.9% of harmful U.V. rays
- Lightweight Nylon Frame
- Built on Side Shields for added protection



TECHNICAL DATA FOR: 81110

| | | | |
|------------------------|--------------------------|--------------------------|-----------------|
| Series | Prodigy | Scratch Resistant | Yes |
| Category | Safety Glasses | Frame Material | Nylon |
| | | Packaging | White Inner Box |
| Case Pack | 144 pair | MIL - PRF - 31013 | N/A |
| Case Dimensions | 22.441 x 14.173 x 13.386 | ANSI Z87+ | Yes |
| Case Weight | 18.801 oz. | AS/NZS 1337.1 | N/A |
| Made In | China | CE EN166 | N/A |

| Item No: | Lens Options: | Lens Coating: | Scratch Resistant: | VLT%: | Frame Color: | Temple Color: | Temple Sleeve: |
|----------|---------------|--------------------|--------------------|-------|--------------|---------------|----------------|
| 81110 | Clear | Duramass Hard Coat | Yes | 90 | Black | Black | N/A |
| 81112 | Gray | Duramass Hard Coat | Yes | 13 | Black | Black | N/A |
| 82110 | Clear | Duramass Hard Coat | Yes | 90 | Navy | Navy | N/A |
| 85110 | Clear | Duramass Hard Coat | Yes | 90 | Black | Black | N/A |

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2017 MCR Safety - All Rights Reserved