



MCR
SAFETY

Stryker

Goggles

Series

Specification Sheet

PRODUCT DESCRIPTION:

MCR Safety® offers a full line of goggles to fit a variety of users and applications. Our Stryker™ has a more modern and stylish look, Duramass® Anti-fog and Anti-Scratch coatings and indirect ventilation. Easy to adjust strap design allows each user a personal fit.

FEATURES:

- Updated stylish look
- Exclusive Duramass® scratch resistant coating
- Comfortable seal around the face
- Elastic or Rubber adjustable strap
- Manufactured in an ISO 9001 certified facility



TECHNICAL DATA FOR: 2310AF

Brand	MCR Safety	Anti-Fog	Anti-Fog
Series	Stryker	Scratch Resistant	Yes
Category	Goggles	Frame Material	PVC
Dielectric	Yes	Packaging	White Inner Box
Case Pack	60 pair	MIL - PRF - 31013	N/A
Case Dimensions	18.110 x 14.567 x 19.291	ANSI Z87+	Yes
Case Weight	15.000 oz.	AS/NZS 1337.1	N/A
Made In	Taiwan	CE EN166	N/A

Item No:	Lens Options:	Lens Coating:	Scratch Resistant:	VLT%:	Frame Color:	Temple Color:	Temple Sleeve:
2310AF	Clear	Duramass Anti-Fog	Yes	90	Smoke	N/A	N/A
2312AF	Gray	Duramass Anti-Fog	Yes	13	Smoke	N/A	N/A
2320AF	Clear	Duramass Anti-Fog	Yes	90	Smoke	N/A	N/A
2322AF	Gray	Duramass Anti-Fog	Yes	13	Smoke	N/A	N/A

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2016 MCR Safety - All Rights Reserved