



MCR
SAFETY

6020

NitriShield

Disposable

Specification Sheet

PRODUCT DESCRIPTION:

Nitrile gloves are made of synthetic latex. They contain no latex proteins and offer excellent resistance to punctures and tears. Nitrile gloves are three times more puncture resistant than rubber and can be used to offer superior resistance to many types of chemicals. This glove is an excellent alternative for individuals who experience allergic reactions to latex. The 6020 is a industrial / food service grade powdered nitrile glove that measures 4 mil in thickness and is 9.5 inches in length.

FEATURES:

- 4 mil, Blue Powdered Nitrile
- Component materials comply with all federal regulations for food contact
- Rolled Cuff
- Textured Grip
- 9.5 Inch Length

APPLICATIONS:

Janitorial , Nursing Home Care, Painting, Food service, Canning



TECHNICAL DATA FOR: 6020

| | | | |
|-----------------------|-------------|-----------------------|---------------|
| Series | NitriShield | Overall Length | 9.5 in. |
| Material Group | Unsupported | FDA Compliant | FDA Compliant |
| Product Type | Disposable | | |
| Size | Large | | |
| Material | Nitrile | | |
| Grade | Premium | | |
| Features | Reversible | | |
| Lining | Unlined | | |
| Pattern | Reversible | | |
| Thumb Style | Wing | | |




MCR
SAFETY

6020

NitriShield

Disposable

Specification Sheet



| Item No: | Size: | A: | B: | C: | Case Weight | UOM Weight |
|----------|------------|--------|-------|-----|-------------|------------|
| 6020L | Large | 9.685 | 4.763 | N/A | 15.700 lb. | 15.700 |
| 6020M | Medium | 9.606 | 4.567 | N/A | 15.100 lb. | 15.100 |
| 6020S | Small | 9.291 | 4.135 | N/A | 14.700 lb. | 14.700 |
| 6020XL | X - Large | 10.000 | 5.236 | N/A | 16.975 lb. | 16.975 |
| 6020XXL | XX - Large | 0 | 0 | N/A | 18.020 lb. | 18.020 |

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2016 MCR Safety - All Rights Reserved