



SPECIFICATION SHEET

63-3314PF

AMBI-DEX® OVERDRIVE EC DISPOSABLE NITRILE GLOVE, POWDER FREE WITH TEXTURED GRIP - 6 MIL

- Economical puncture resistance with great comfort, dexterity and tactile sensitivity
- Textured grip provides a good grip in wet or dry environments
- Contains no natural rubber latex proteins
- Ambidextrous for quick and easy donning
- Powder-Free for clean comfort and superior tactile sensitivity
- Complies with FDA food handling requirements, 21 CFR 177.2600
- 14" length extended cuff

APPLICATIONS

- Industrial
- Sanitation
- Plumbing

TECHNICAL DATA

MATERIAL	Nitrile			
COLOR	Blue			
SIZES	S - XL			
PACKAGING	50 per box; 10 boxes per case (500 pcs)			
CASE	16.1" x 11.9" x 9.9" / 41.0cm x 30.1cm x 25.1cm			
CASE WEIGHT	S	M	L	XL
	10.4 lbs 4.7 kg	11.4 lbs 5.2 kg	12.0 lbs 5.4 kg	12.7 lbs 5.8 kg
COO	Malaysia			

ELONGATION INFORMATION

BEFORE AGING		AFTER ACCELERATED AGING	
Tensile Strength (minimum)	Elongation (minimum)	Tensile Strength (minimum)	Elongation (minimum)
(Mpa)	%	(Mpa)	%
14	500	14	400

BARCODES

ITEM	BAG	DISPENSER	CASE
63-3314PF/S	---	616314034466	02616314034466
63-3314PF/M	---	616314034459	02616314034459
63-3314PF/L	---	616314034442	02616314034442
63-3314PF/XL	---	616314034473	02616314034473



DIMENSIONS (in/cm)

	S	M	L	XL
A	14 / 23.5	14 / 24.0	14 / 24.0	14 / 24.0
B	3.3 / 8.5	3.9 / 9.8	4.2 / 10.7	4.6 / 11.7

Palm Thickness 0.15mm (+/- - 0.02mm) / Cuff Thickness 0.09mm (+/- - 0.02mm)
Finger Tip Thickness 0.19mm (+/- - 0.02mm)

