

XGC Extension Cable



NOCO

Boost Accessories™

Extended **weatherproof** connections.

Extend the reach of the Boost 12V input/output charging accessory & XGC powered products.

XGC is a universal connector system for extending the reach of the Genius Boost 12V input/output charging accessory and the distance of your XGC powered products. It provides higher current carrying ability over traditional connector systems, and delivers safe and reliable power with minimal voltage loss. It has molded strain reliefs to relieve unwanted tension, and is dirt, dust and water resistant for optimal performance in harsh environments. For use with the XGS4 and XGS9 solar panel battery chargers, their compatible FLEX, and the GB70 and GB150 jump starters.



Ultra**Safe**™

All NOCO products are tested with safety as the top priority with non-toxic materials and quality manufacturing.

Heavy Duty
Design

From custom engineered strain reliefs to heavy guage wire, NOCO accessories are dirt, water, UV, and impact resistant.

8^{AWG}



Made from durable, high-performance 8AWG silicone wire that maintains its flexibility in cold weather environments.


Universal
Compatibility

Compatible with the GB70 & GB150 jump starters and XGS solar panel battery chargers, along with solar FLEX regulators.

GC028 | GC029 | GC030

Connects to the **GB70** or **GB150** 12V IN/OUT port for fast charging or powering 12V devices. Also connects to **XGS solar panels** and their compatible FLEX regulators to recharge portable battery packs or to charge your 12V lead-acid car battery.

GC028 XGC 2' Extension Cable



Technical Specifications

Input:	XGC Female
Output:	XGC Male
Wire Size:	Duplex 16AWG
Length:	2 ft

Compatible Models:

XGS4	GB70	FLEX Regulators
XGS9	GB150	

Retail Packaging:

Dimensions: 1.6"x5.1"x3.2"
Weight: 0.13 lbs
UPC: 0-46221-13124-6

Inner Carton:

Dimensions: 1.8"x5.4"x3.5"
Weight: 0.18 lbs

Master Carton:

Dimensions: 11.3"x12.0"x11.6"
Weight: 7.76 lbs

Quantity: 36

UCC: 10046221131243

Units Per Pallet: 1,728 Units

GC029 XGC 8' Extension Cable



Technical Specifications

Input:	XGC Female
Output:	XGC Male
Wire Size:	Duplex 16AWG
Length:	8 ft

Compatible Models:

XGS4	GB70	FLEX Regulators
XGS9	GB150	

Retail Packaging:

Dimensions: 1.6"x5.1"x3.2"
Weight: 0.32 lbs
UPC: 0-46221-13125-3

Inner Carton:

Dimensions: 1.8"x5.4"x3.5"
Weight: 0.37 lbs

Master Carton:


Dimensions: 11.3"x12.0"x11.6"
Weight: 14.57 lbs

Quantity: 36

UCC: 10046221131250

Units Per Pallet: 1,728 Units

GC030 XGC 25' Extension Cable



Technical Specifications

Input:	XGC Female
Output:	XGC Male
Wire Size:	Duplex 16AWG
Length:	25 ft

Compatible Models:

XGS4	GB70	FLEX Regulators
XGS9	GB150	

Retail Packaging:

Dimensions: 2.4"x7.1"x2.8"
Weight: 0.88 lbs
UPC: 0-46221-13130-7

Inner Carton:

Dimensions: 2.4"x7.3"x3.0"
Weight: 0.97 lbs

Master Carton:

Dimensions: 15.3"x16.5"x10.2"
Weight: 36.24 lbs

Quantity: 36

UCC: 10046221131304

Units Per Pallet: 1,080 Units