



4700 W. 160th St.
Cleveland, OH 44135
PH:800-321-9532
FX:800-321-9535
www.oatey.com

TECHNICAL SPECIFICATION

**140 SERIES / 101 PNC SERIES
BRASS AND PLASTIC
NO-CALK SHOWER DRAIN**



TECHNICAL SPECIFICATION: Oatey Brass and Plastic No-Calk Shower Drains are designed for use with preformed shower stall bases. The drain body is sealed to the shower base with a fiber and rubber washer. 2" Schedule 40 DWV pipe is secured with a mechanically compressed gasket that does not require caulking. Drain top accommodates 4-1/4" Universal Snap-Tite Strainers available in a variety of designer finishes.



PHYSICAL/CHEMICAL PROPERTIES

Drain Body Material Cast Brass Metal
 ABS Plastic = Black
 PVC Plastic = White

COMMON APPLICATIONS

Oatey No-Calk Shower Drains are designed for use with preformed shower stall bases. The drain body is sealed to the shower base with a fiber and rubber washer. 2" Schedule 40 DWV pipe is secured with a mechanically compressed gasket that does not require caulking. Drain top accommodates 4-1/4" Universal Snap-Tite Strainers available in a variety of designer finishes.

- Made of Cast Brass or Plastic
- Ideal for Slab Construction
- Available with 4.25" Stainless Steel or UltraShine PVD Polished Brass Snap-Tite Strainer
- Compression gasket tightens around 2" Schedule 40 DWV pipe with caulking nut and wrench
- Can be used with 1-1/2" Schedule 40 DWV pipe and 1-1/2" or 2" Copper DWV pipe when caulking gasket is replaced

	PRODUCT NUMBER	DESCRIPTION	PACK	CARTON WEIGHT
	42150	Brass No-Calk Shower Drain w/Stainless Steel Strainer	12	20 lbs.
	42084	ABS No-Calk Shower Drain w/Stainless Steel Strainer	12	7 lbs.
	42099	PVC No-Calk Shower Drain w/Stainless Steel Strainer	12	8 lbs.
	42077	ABS No-Calk Shower Drain w/White Plastic Strainer	12	6 lbs.
	42075	PVC No-Calk Shower Drain w/White Plastic Strainer	12	8 lbs.
	42080	PVC No-Calk Shower Drain w/ UltraShine® PVD Polished Brass Strainer	12	8 lbs.
NO-CALK SHOWER DRAIN ACCESSORIES				
	42163	Caulking Gasket for 1-1/2" Schedule 40 DWV	12	1 lb.
	42156	Caulking Gasket for 2" Schedule 40 DWV	12	1 lb.
	42157	Rubber Caulking gasket to fit 2" No-hub cast iron pipe	12	1 lb.
	42159	Caulking Gasket for 1-1/2" Copper DWV	12	1 lb.
	42158	Caulking Gasket for 2" Copper DWV	12	1 lb.
	42239	NO-CALK shower drain wrench- carded	4	5lbs.