



4700 W. 160th St.
Cleveland, Ohio 44135
Ph: (800) 321-9532
Fax: (800) 321-9535
www.oatey.com



74000 Series PVC Adjustable General Purpose Cleanout Cast Barrel With 6" Round Cover With Round Top



SUBMITTAL SPECIFICATION

Engineering Specification: Oatey adjustable general purpose cleanouts are used for general service in restaurants, restrooms and other commercial applications where traffic is expected. Barrel assembly is completely adjustable to meet the finished floor height.

Job Reference



(All dimensions in inches)

- Barrel diameter is 3-1/2 in. IPS thread.
- Primer tap knock-out is 1/2 in. FIP thread.

✓	Socket Size (C)	Base Material	Cover Finish	Part Number
	3 or 4 in. Pipe Fit	PVC	Brass	74217
	3 or 4 in. Pipe Fit	PVC	Nickel	74227
	3 or 4 in. Pipe Fit	PVC	Chrome	74237
	4 in. Pipe Fit	PVC	Brass	74218
	4 in. Pipe Fit	PVC	Nickel	74228
	4 in. Pipe Fit	PVC	Chrome	74238
	4 in. Hub Fit	PVC	Brass	74219
	4 in. Hub Fit	PVC	Nickel	74229
	4 in. Hub Fit	PVC	Chrome	74239

	Dimensional Data		
	A	B	C
3 in.	4.75 in.	1.00 – 3.75 in.	3 in. Hub, 4 in. Pipe
4 in.	5.00 in.	1.00 – 3.75 in.	4 in. Pipe
4 in.	2.00 in.	1.00 – 3.75 in.	4 in. Hub

*3 in. plug included in barrel.

Cover Properties	
Finish	Load*
Brass	Medium
Nickel	Medium
Chrome	Medium

*Load is defined by ASME A112.21.1M.
Light Duty – Safe live load under 2000 lbs.
Medium Duty – Safe live load between 2000 lbs. and 4999 lbs.



4700 W. 160th St.
Cleveland, Ohio 44135
Ph: (800) 321-9532
Fax: (800) 321-9535
www.oatey.com

84000 Series



ABS Adjustable General Purpose Cleanout Cast Barrel With 6" Round Cover With Round Top



SUBMITTAL SPECIFICATION

Engineering Specification: Oatey adjustable general purpose cleanouts are used for general service in restaurants, restrooms and other commercial applications where traffic is expected. Barrel assembly is completely adjustable to meet the finished floor height.

Job Reference



(All dimensions in inches)

- Barrel diameter is 3-1/2 in. IPS thread.
- Primer tap knock-out is 1/2 in. FIP thread.

✓	Socket Size (C)	Base Material	Cover Finish	Part Number
	3 or 4 in. Pipe Fit	ABS	Brass	84217
	3 or 4 in. Pipe Fit	ABS	Nickel	84227
	3 or 4 in. Pipe Fit	ABS	Chrome	84237
	4 in. Pipe Fit	ABS	Brass	84218
	4 in. Pipe Fit	ABS	Nickel	84228
	4 in. Pipe Fit	ABS	Chrome	84238
	4 in. Hub Fit	ABS	Brass	84219
	4 in. Hub Fit	ABS	Nickel	84229
	4 in. Hub Fit	ABS	Chrome	84239

	Dimensional Data		
	A	B	C
3 in.	4.75 in.	1.00 – 3.75 in.	3 in. Hub, 4 in. Pipe
4 in.	5.00 in.	1.00 – 3.75 in.	4 in. Pipe
4 in.	2.00 in.	1.00 – 3.75 in.	4 in. Hub

*3 in. plug included in barrel.

Cover Properties	
Finish	Load*
Brass	Medium
Nickel	Medium
Chrome	Medium

*Load is defined by ASME A112.21.1M.

Light Duty – Safe live load under 2000 lbs.

Medium Duty – Safe live load between 2000 lbs. and 4999 lbs.